



# eW Cove MX Powercore

**eW Cove MX Powercore, 4000 K, 125° x 120° Beam Angle, 12.5 W/ft, 1.2 m (4 ft)**

eW Cove MX Powercore, 4000 K, 125° x 120° Beam Angle, 12.5 W/ft, 1.2 m (4 ft)

With its superior light output, wide beam angle, and range of fixed colors and color temperatures, eW Cove MX Powercore can be used for accent lighting and indirect general illumination, as well as the full range of wall and ceiling cove applications. This fixture meets or exceeds the performance of comparable linear fluorescent strip cove lights while lowering installation, energy, and maintenance costs. eW Cove MX Powercore offers environmentally conscious buyers a green, energy-efficient lighting solution without sacrificing quality or quantity of light. Integrated Powercore technology ensures rapid, efficient and accurate control of power output to the fixture directly from line voltage, eliminating the need for external power supplies. Use of standard wiring dramatically simplifies installation and helps lower total system cost.

## Product data

General information	
Number of light sources	10 [ 10 pcs]
Lamp family code	LED-HB [ LED High Brightness]
Light source colour	Neutral white
Light source replaceable	No
Driver/power unit/transformer	PSR [ Power supply unit regulating]
Driver included	Yes
Optic type	WB [ Wide beam]
Optical cover/lens type	PC [ Polycarbonate bowl/cover]

Luminaire light beam spread	125° x 120°
Protection class IEC	Safety class I (I)
Ready-to-install	Ready-to-install
Type description	No
CE mark	CE mark
UL mark	UL and cUL mark
CCC mark	CCC mark


eW Cove MX Powercore

Operating and electrical	
Input Voltage	100 to 277 V
Input frequency	50 to 60 Hz
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Housing material	Aluminum die-cast
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Length	1220 mm
Colour	White
Approval and application	
Ingress protection code	IP20 [ Finger-protected]
FCC mark	FCC Class B
Initial performance (IEC compliant)	
Initial luminous flux (system flux)	2809 lm
Initial luminous flux at colour temperature of 4,000 K	2809 lm
Initial LED luminaire efficacy	53.1 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	83
Initial input power	50 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25 °C Calculated	100000

Lumen Maintenance 50% at 25 °C Reported	65000
Lumen Maintenance 50% at 50 °C Calculated	100000
Lumen Maintenance 50% at 50 °C Reported	65000
Lumen Maintenance 70% at 25 °C Calculated	100000
Lumen Maintenance 70% at 25 °C Reported	65000
Lumen Maintenance 70% at 50 °C Calculated	100000
Lumen Maintenance 70% at 50 °C Reported	65000
Application conditions	
Ambient temperature range	-20 to +50 °C
Maximum dimming level	10% (depends on dimmer, ELV)
Suitable for random switching	Yes
Product data	
Full product code	871829137860099
Order product name	BCX416 10xLED-HB/4000 100-277V L1220 WB
EAN/UPC – product	8718291378600
Order code	523-000050-25
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	910503702753
Net Weight (Piece)	1.800 kg
Commercial Code	523-000050-25
Catalogue number description	eW Cove MX Powercore, 4000 K, 125° x 120° Beam Angle, 12.5 W/ft, 1.2 m (4 ft)



Dimensional drawing



BCX416 10xLED-HB/4000 100-277V L1220 WB

