



# ColorGraze QLX Powercore

## ColorGraze QLX Powercore, RGB, 30° x 60° Beam Angle, 914 mm (3 ft)

ColorGraze QLX Powercore, RGB, 30° x 60° Beam Angle, 914 mm (3 ft)

Many architectural structures need a linear fixture capable of illuminating several storeys with minimal setback and reduced power consumption. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasize their brands. Graze QLX Powercore is capable of illuminating over 10 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

### Product data

<b>General Information</b>		<b>Input frequency</b>	
Lamp family code	LED-HB [ LED High Brightness]	50 to 60 Hz	
Light source colour	RGB	<b>Controls and Dimming</b>	
Light source replaceable	No	Dimmable	
Driver included	Yes	Yes	
Luminaire light beam spread	30° x 60°	<b>Mechanical and Housing</b>	
Protection class IEC	Safety class I (I)	Housing material	
CE mark	CE mark	Aluminum extruded	
UL mark	UL and cUL mark	Optic material	
Lifetime to 70% luminous flux	100000 h	Optical cover/lens material	
<b>Operating and Electrical</b>		Polycarbonate	
Input Voltage		Length	
100 to 277 V		914 mm	
		Colour	
		aluminium	

ColorGrazex QLX Powercore

Approval and Application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [ 20 J vandal-resistant]
Vibration standard	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.
Vibration rating	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.

Initial Performance (IEC Compliant)	
Initial input power	45 W

Over Time Performance (IEC Compliant)	
Lumen Maintenance 50% at 25 °C	100000
Calculated	
Lumen Maintenance 50% at 25 °C	100000
Reported	
Lumen Maintenance 50% at 50 °C	80000
Calculated	
Lumen Maintenance 50% at 50 °C	80000
Reported	
Lumen Maintenance 70% at 25 °C	60000
Calculated	

Lumen Maintenance 70% at 25 °C	100000
Reported	
Lumen Maintenance 70% at 50 °C	60000
Calculated	
Lumen Maintenance 70% at 50 °C	91000
Reported	

Application Conditions	
Ambient temperature range	-40 to +50 °C

Product Data	
Full product code	871829160384900
Order product name	BCS467 30x60 RGB L914
EAN/UPC – product	8718291603849
Order code	123-000079-33
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910503703360
SAP net weight (piece)	3.800 kg
Commercial Code	123-000079-33
Catalogue number description	ColorGrazex QLX Powercore, RGB, 30° x 60° Beam Angle, 914 mm (3 ft)



Dimensional drawing



