



# ColorGraz QLX Powercore

## ColorGraz QLX Powercore, RGB, 15° x 30° Beam Angle, 1219 mm (4 ft)

ColorGraz QLX Powercore, RGB, 15° x 30° Beam Angle, 1219 mm (4 ft)

Many architectural structures need a linear fixture capable of illuminating several storeys with minimal setback and reduced power consumption. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasize their brands. Graze QLX Powercore is capable of illuminating over 10 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

### Product data

<b>General Information</b>		<b>Input frequency</b>	
Lamp family code	LED-HB [ LED High Brightness]	50 to 60 Hz	
Light source colour	RGB	<b>Controls and Dimming</b>	
Light source replaceable	No	Dimmable	
Driver included	Yes	Yes	
Luminaire light beam spread	15° x 30°	<b>Mechanical and Housing</b>	
Protection class IEC	Safety class I (I)	Housing material	
CE mark	CE mark	Aluminum extruded	
UL mark	UL and cUL mark	Optic material	
Lifetime to 70% luminous flux	100000 h	Optical cover/lens material	
<b>Operating and Electrical</b>		Polycarbonate	
Input Voltage		Length	
100 to 277 V		1219 mm	
		Colour	
		aluminium	


ColorGraze QLX Powercore

Approval and Application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [ 20 J vandal-resistant]
Vibration standard	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.
Vibration rating	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.

Initial Performance (IEC Compliant)	
Initial input power	60 W

Over Time Performance (IEC Compliant)	
Lumen Maintenance 50% at 25 °C	100000
Calculated	
Lumen Maintenance 50% at 25 °C	100000
Reported	
Lumen Maintenance 50% at 50 °C	80000
Calculated	
Lumen Maintenance 50% at 50 °C	80000
Reported	
Lumen Maintenance 70% at 25 °C	60000
Calculated	

Dimensional drawing



Lumen Maintenance 70% at 25 °C	100000
Reported	
Lumen Maintenance 70% at 50 °C	60000
Calculated	
Lumen Maintenance 70% at 50 °C	91000
Reported	

Application Conditions	
Ambient temperature range	-40 to +50 °C

Product Data	
Full product code	871829160388700
Order product name	BCS467 15x30 RGB L1219
EAN/UPC – product	8718291603887
Order code	123-000079-37
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910503703364
SAP net weight (piece)	4.700 kg
Commercial Code	123-000079-37
Catalogue number description	ColorGraze QLX Powercore, RGB, 15° x 30° Beam Angle, 1219 mm (4 ft)

