



ColorGrazec EC Powercore

ColorGrazec EC Powercore, RGB, 90° x 90° Beam Angle, 1219 mm (4 ft)

ColorGrazec EC Powercore, RGB, 90° x 90° Beam Angle, 1219 mm (4 ft)

Some exterior architectural details require a soft-edged volume fill of light. Graze EC Powercore combines this output with the proven, durable design of the Graze Powercore product family and low power consumption.

Product data

General Information		Input frequency	
Lamp family code	LED-HB [LED High Brightness]	50 to 60 Hz	
Lamp colour code	RGB	Controls and Dimming	
Light source replaceable	No	Dimmable	Yes
Driver included	Yes	Mechanical and Housing	
Optic type	WB [Wide beam]	Housing material	Aluminum extruded
Optical cover/lens type	PCF [Polycarbonate bowl/cover frosted]	Optic material	Polycarbonate
Luminaire light beam spread	90° x 90°	Optical cover/lens material	Polycarbonate
Protection class IEC	Safety class I (I)	Length	1219 mm
CE mark	CE mark	Colour	Aluminium
UL mark	UL and cUL mark	Approval and Application	
Lifetime to 70% luminous flux	80000 h	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Operating and Electrical		Mech. impact protection code	IK08 [5 J vandal-protected]
Input Voltage	100 to 277 V		

ColorGraze EC Powercore

Vibration standard	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.
Vibration rating	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	964 lm
Initial LED luminaire efficacy	15.4 lm/W
Initial input power	40 W

Over Time Performance (IEC Compliant)

Lumen Maintenance 50% at 25 °C	100000
Reported	
Lumen Maintenance 50% at 50 °C	80000
Reported	
Lumen Maintenance 70% at 25 °C	80000
Reported	

Lumen Maintenance 70% at 50 °C	60000
Reported	

Application Conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Product Data

Full product code	871829160392400
Order product name	BCS468 RGB L1219
EAN/UPC – product	8718291603924
Order code	123-000079-43
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910503703370
SAP net weight (piece)	4.700 kg
Commercial Code	123-000079-43
Commercial Code	ColorGraze EC Powercore, RGB, 90° x 90° Beam Angle, 1219 mm (4 ft)



Dimensional drawing

