



# eColor Graze QLX Powercore

**eColor Graze QLX Powercore, Amber, 10° x 60°  
Beam Angle, 305 mm (1 ft)**

Amber - 10° x 60° - 305 mm - Aluminum

Many architectural structures need a linear fixture capable of illuminating several storeys with minimal setback and reduced power consumption. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasize their brands. Graze QLX Powercore is capable of illuminating over 10 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

## Product data

General Information		Input frequency	
Lamp family code	LED-HB [ LED High Brightness]	50 to 60 Hz	
Light source colour	Amber	Controls and Dimming	
Light source replaceable	No	Dimmable	Yes
Driver included	Yes	Mechanical and Housing	
Optical cover/lens type	PC-UV [ Polycarbonate bowl/cover UV-resistant]	Housing material	Aluminum extruded
Luminaire light beam spread	10° x 60°	Optic material	Polycarbonate
Protection class IEC	Safety class I (I)	Optical cover/lens material	Polycarbonate
CE mark	CE mark	Length	305 mm
UL mark	UL and cUL mark	Colour	Aluminum
Lifetime to 70% luminous flux	100000 h	Approval and Application	
Operating and Electrical		Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Input Voltage	100 to 277 V	Mech. impact protection code	IK10 [ 20 J vandal-resistant]

eColor Graze Q LX Powercore

Vibration standard	Complies with ANSI C136.31, 3G
Vibration rating	Complies with ANSI C136.31, 3G
Initial Performance (IEC Compliant)	
Initial input power	15 W
Application Conditions	
Ambient temperature range	-40 to +50 °C
Product Data	
Full product code	871829160674199
Order product name	BCS447 10x60 AM L305

EAN/UPC – product	8718291606741
Order code	223-000081-07
SAP numerator – quantity per pack 1	
Numerator – packs per outer box	4
SAP material	910503703476
Net Weight (Piece)	1.200 kg
Commercial Code	223-000081-07
Commercial Code	eColor Graze Q LX Powercore, Amber, 10° x 60° Beam Angle, 305 mm (1 ft)



Dimensional drawing

