



eW Graze MX Powercore

BCS419 10x60/5500 L914

eW Graze MX Powercore, 5500 K, 10° x 60° Beam Angle, 914 mm (3 ft)

Many architectural structures need a linear fixture capable of illuminating multiple storeys with minimal setback. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasise their brands. Graze MX Powercore is capable of illuminating over 20 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

Product data

General Information		Controls and Dimming	
Lamp family code	LED-HB [LED High Brightness]	Dimmable	Yes
Lamp colour code	Neutral white		
Light source replaceable	No	Mechanical and Housing	
Driver included	Yes	Housing material	Aluminum extruded
Luminaire light beam spread	10° x 60°	Optical cover/lens material	Polycarbonate
Protection class IEC	Safety class I (I)	Length	914 mm
CE mark	CE mark		
UL mark	UL and cUL mark	Approval and Application	
Lifetime to 70% luminous flux	60000 h	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
		Mech. impact protection code	IK10 [20 J vandal-resistant]
Operating and Electrical		Vibration standard	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.
Input Voltage	100 to 277 V		
Input frequency	50 to 60 Hz		

eW Graze MX Powercore

Vibration rating	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.
------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Initial Performance (IEC Compliant)

Lamp colour temperature	5500 K
Initial input power	42 W

Over Time Performance (IEC Compliant)

Lumen Maintenance 50% at 25 °C	60000
Reported	
Lumen Maintenance 50% at 50 °C	60000
Reported	
Lumen Maintenance 70% at 25 °C	60000
Reported	
Lumen Maintenance 70% at 50 °C	60000
Reported	

Application Conditions	
Ambient temperature range	-20 to +50 °C
Product Data	
Full product code	871829161048900
Order product name	BCS419 10x60/5500 L914
EAN/UPC – product	8718291610489
Order code	523-000080-35
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910503703723
SAP net weight (piece)	3.800 kg
Commercial Code	523-000080-35
Commercial Code	eW Graze MX Powercore, 5500 K, 10° x 60° Beam Angle, 914 mm (3 ft)



Dimensional drawing

