



eW Graze EC Powercore

BCS428 4000 L305

eW Graze EC Powercore, 4000 K, 90° x 90° Beam Angle, 305 mm (1 ft)

Some exterior architectural details require a soft-edged volume fill of light. Graze EC Powercore combines this output with the proven, durable design of the Graze Powercore product family and low power consumption.

Product data

General Information		Controls and Dimming	
Lamp family code	LED-HB [LED High Brightness]	Dimmable	Yes
Lamp colour code	Neutral white		
Light source replaceable	No	Mechanical and Housing	
Driver included	Yes	Housing material	Aluminum extruded
Optical cover/lens type	PCF [Polycarbonate bowl/cover frosted]	Optic material	Polycarbonate
Luminaire light beam spread	90° x 90°	Optical cover/lens material	Polycarbonate
Protection class IEC	Safety class I (I)	Length	305 mm
CE mark	CE mark	Colour	Aluminium
UL mark	UL and cUL mark	Approval and Application	
Lifetime to 70% luminous flux	36000 h	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Operating and Electrical		Mech. impact protection code	IK10 [20 J vandal-resistant]
Input Voltage	100 to 277 V	Vibration standard	Complies with ANSI C136.31, 3G
Input frequency	50 to 60 Hz	Vibration rating	Complies with ANSI C136.31, 3G

eW Graze EC Powercore

Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	245 lm
Lamp colour temperature	4000 K
Colour Rendering Index	87
Initial input power	15 W


Over Time Performance (IEC Compliant)	
Lumen Maintenance 50% at 25 °C Reported	36000
Lumen Maintenance 50% at 50 °C Reported	36000
Lumen Maintenance 70% at 25 °C Reported	36000
Lumen Maintenance 70% at 50 °C Reported	36000

Application Conditions	
Ambient temperature range	-40 to +50 °C

Product Data	
Full product code	871829161194399
Order product name	BCS428 4000 L305
EAN/UPC – product	8718291611943
Order code	523-000082-01
SAP numerator – quantity per pack	1
Numerator – packs per outer box	4
SAP material	910503703808
SAP net weight (piece)	1.200 kg
Commercial Code	523-000082-01
Commercial Code	eW Graze EC Powercore, 4000 K, 90° x 90° Beam Angle, 305 mm (1 ft)



Dimensional drawing



BCS428 4000 L305

