



Vaya Linear LP

BCP422 28x84 3000 L1200 CE

Philips Vaya Linear LP white, mono and RGB is a reliable and cost effective LED lighting fixture designed for static or dynamic lighting effects. Vaya Linear LP is ideal for exterior cove lighting and low-level grazing applications with a wide 120° beam or elliptical 28 x 84° optics. Two lengths and a wide range of available color temperatures make this product versatile and easy to use. Input and output connectors make installations fast, easy and reliable.

Product data

| General Information | | Mechanical and Housing | |
|-------------------------------|-------------------------------|--|---|
| Lamp family code | LED-HB [LED High Brightness] | Housing Material | Aluminum extruded |
| Beam angle of light source | 28 x 84 ° | Optic material | Glass |
| Light source color | Neutral white | Optical cover/lens material | Tempered glass |
| Light source replaceable | No | Optical cover/lens shape | Flat |
| Driver included | Yes | Optical cover/lens finish | Clear |
| Optical cover/lens type | GC [Clear glass] | Length | 1200 mm |
| Luminaire light beam spread | 28° | Approval and Application | |
| CE mark | CE mark | Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| UL mark | - | Mech. impact protection code | IK07 [2 J reinforced] |
| CQC mark | - | Initial Performance (IEC Compliant) | |
| Lifetime to 70% luminous flux | 50000 h | Initial luminous flux (system flux) | 1129 lm |
| PSE mark | PSE mark | Initial LED luminaire efficacy | 65.5 lm/W |
| Operating and Electrical | | Init. Corr. Color Temperature | 3000 K |
| Input Voltage | 100 to 240 V | Over Time Performance (IEC Compliant) | |
| Input Frequency | 50 to 60 Hz | Lumen Maintenance 70% at 25°C Reported | 60000 |
| Controls and Dimming | | Lumen Maintenance 70% at 40°C Reported | 60000 |
| Dimmable | No | Lumen Maintenance 80% at 25°C Reported | 60000 |

Vaya Linear LP

| | |
|--|-------|
| Lumen Maintenance 80% at 40°C Reported | 60000 |
| Lumen Maintenance 90% at 25°C Reported | 33000 |
| Lumen Maintenance 90% at 40°C Reported | 32000 |

Application Conditions

| | |
|---------------------------|----------------|
| Ambient temperature range | -40 to +104 °F |
|---------------------------|----------------|


Product Data

| | |
|--------------------|----------------------------|
| Order product name | BCP422 28x84 3000 L1200 CE |
| EAN/UPC - Product | 8718291620402 |

| | |
|---------------------------------|--------------|
| Order code | 910503704436 |
| Local order code | . |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 4 |
| Material Nr. (12NC) | 910503704436 |
| Net Weight (Piece) | 2.150 kg |



Dimensional drawing



Vaya

