



# Vaya Linear LP

## BCP423 28x84 AM L1200 CE

Philips Vaya Linear LP white, mono and RGB is a reliable and cost effective LED lighting fixture designed for static or dynamic lighting effects. Vaya Linear LP is ideal for exterior cove lighting and low-level grazing applications with a wide 120° beam or elliptical 28 x 84° optics. Two lengths and a wide range of available color temperatures make this product versatile and easy to use. Input and output connectors make installations fast, easy and reliable.

### Product data

| General Information           |                               | Mechanical and Housing              |   |
|-------------------------------|-------------------------------|-------------------------------------|---|
| Lamp family code              | LED-HB [ LED High Brightness] | Housing material                    | Aluminum extruded                             |
| Beam angle of light source    | 28 x 84 °                     | Optic material                      | Glass   |
| Light source colour           | Amber                         | Optical cover/lens material         | Tempered glass                                |
| Light source replaceable      | No                            | Optical cover/lens shape            | Flat  |
| Driver included               | Yes                           | Optical cover/lens finish           | Clear   |
| Optical cover/lens type       | GC [ Clear glass]             | Length                              | 1200 mm                                       |
| Luminaire light beam spread   | 28°                           | Colour                              | Dark gray                                     |
| CE mark                       | CE mark                       | Approval and Application            |   |
| UL mark                       | -                             | Ingress protection code             | IP66 [ Dust penetration-protected, jet-proof] |
| CQC mark                      | -                             | Mech. impact protection code        | IK07 [ 2 J reinforced]                        |
| Lifetime to 70% luminous flux | 50000 h                       | Initial Performance (IEC Compliant) |   |
| Operating and Electrical      |                               | Initial luminous flux               | 1200 lm                                       |
| Input voltage                 | 100 to 240 V                  | Application Conditions              |   |
| Input frequency               | 50 to 60 Hz                   | Ambient temperature range           | -40 to +40 °C                                 |
| Controls and Dimming          |                               | Product Data                        |   |
| Dimmable                      | No                            | Full product code                   | 871829162100399                               |


Vaya Linear LP

|                                 |                          |
|---------------------------------|--------------------------|
| Order product name              | BCP423 28x84 AM L1200 CE |
| EAN/UPC – product               | 8718291621003            |
| Order code                      | 62100399                 |
| Numerator – quantity per pack   | 1                        |
| Numerator – packs per outer box | 4                        |

|                     |              |
|---------------------|--------------|
| Material no. (12NC) | 910503704496 |
| Net weight (piece)  | 2.150 kg     |



Dimensional drawing



Vaya

