



LuxSpace square, recessed

DN572B LED24S/840 PSE-E F WH

LuxSpace2 Square, LED module, system flux 2400 lm, 840 neutral white, Power supply unit DC compatible, external, Facetted reflector, White RAL 9003

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

Product data

General Information		
Lamp family code	LED24S [LED module, system flux 2400 lm]	
Cap-Base	- [-]	
Light source replaceable	No	
Number of gear units	1 unit	
Gear	-	
Driver included	Yes	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	
		Service tag
		Yes
		Product family code
		DN572B [LuxSpace2 Square]
		Lighting Technology
		LED
		Value ladder
		Specification
		CE mark
		Yes
		Warranty period
		5 years
		Flammability mark
		For mounting on normally flammable surfaces
		ENEC mark
		ENEC mark
		Glow-wire test
		Temperature 850 °C, duration 5 s

LuxSpace square, recessed

EU RoHS compliant	No
-------------------	----

Light Technical

Luminous Flux	2,500 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	119 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Light source color	840 neutral white
Optic type	Facetted reflector
Optical cover type	-
Luminaire light beam spread	80°
Unified glare rating CEN	19

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	0.24 ms
Power Consumption	21 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	32

Temperature

Ambient temperature range	+10 to +25 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit DC compatible, external
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Steel

Housing Color	White RAL 9003
Optical cover finish	Frosted
Overall length	214 mm
Overall width	214 mm
Overall height	119 mm
Dimensions (Height x Width x Depth)	119 x 214 x 214 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.37) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

Product Data

Order product name	DN572B LED24S/840 PSE-E F WH
Full product name	DN572B LED24S/840 PSE-E F WH
Full product code	871829194058600
Order code	910503706623
Material Nr. (12NC)	910503706623
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291940586
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291940586

LuxSpace square, recessed

