



DecoFlood² DVP628

DVP628 CDM-SA/T150W/942 EB II CO GR MBA

Decoflood Successor, MASTERColour CDM-SA/T, 150 W,
Electronic, Marine salt protected coating

Lighting plays an important role in revealing a town's historical and cultural identity. It is a challenge for municipal authorities to create a cohesive, harmonious lighting scheme while accentuating each part of the town as well as features ranging from landmarks to architectural details. Available in both LED and conventional versions, Decoflood² and MiniDecoflood² floodlights are ideal for illuminating a wide variety of structures, with reflectors for accent and tree lighting, façade and area lighting, and architectural street lighting. The revolutionary ZoomFocus allows – for the first time – easy adjustment of the beam angle while the floodlight is operational. Accessories are discreetly integrated to ensure a pleasant daytime appearance.

Product data

General Information		Mechanical and Housing	
Lamp family code	CDM-SA-T [MASTERColour CDM-SA/T]	Housing Color	Grey
Gear	EB [Electronic]	Mounting device	Mounting bracket adjustable
Product family code	DVP628 [Decoflood Successor]	Parts color	Cover painted
CE mark	Yes	Approval and Application	
ENEC mark	ENEC mark	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Light Technical		Mech. impact protection code	IK08 [5 J vandal-protected]
Light source color	942 neutral white	Protection class IEC	Safety class II
Operating and Electrical		Product Data	
Input Voltage	220 to 240 V	Order product name	DVP628 CDM-SA/T150W/942 EB II CO GR MBA
Power Consumption	150 W	Full product name	DVP628 CDM-SA/T150W/942 EB II CO GR MBA
		Full product code	871829134852800

DecoFlood² DVP628

Order code	910503896418
Material Nr. (12NC)	910503896418
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291348528

Numerator - Packs per outer box	1
EAN/UPC - Case	8718291348528

Dimensional drawing

