



CoreLine Wall-mounted

WL120V LED12S/840 PSU WH

CoreLine Wall-mounted, 18 W, D344 mm, 1200 lm, 4000 K, IP65

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Wall-mounted range of LED products can be used to replace traditional wall-mounted luminaires incorporating compact fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

General Information		Flammability mark	
Lamp family code	LED12S [LED module, system flux 1200 lm]	Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	No	ENEC mark	-
Number of gear units	1 unit	Glow-wire test	Temperature 850 °C, duration 30 s
Driver included	Yes	EU RoHS compliant	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Light Technical	
Lighting Technology	LED	Luminous Flux	1,200 lm
Value ladder	Performance	Correlated Color Temperature (Nom)	4000 K
CE mark	Yes	Luminous Efficacy (rated) (Nom)	67 lm/W
Warranty period	3 years + 2 years upon registration	Color rendering index (CRI)	>80
		Number of light sources	1
		Beam angle of light source	120 degree(s)
		Light source color	840 neutral white
		Optic type	Symmetrical
		Luminaire light beam spread	180°

CoreLine Wall-mounted

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.32 ms
Power Consumption	18 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	15

Temperature	
Ambient temperature range	-20 to +35 °C

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing	
Housing Material	Composite materials
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Polyamide
Housing Color	White
Optical cover finish	Opal
Overall height	120 mm

Overall diameter	344 mm
------------------	--------


Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.37, 0.37) SDCM<3
Power consumption tolerance	+/-10%

Application Conditions	
Performance ambient temperature Tq	25 °C
Suitable for random switching	No

Product Data	
Order product name	WL120V LED12S/840 PSU WH
Full product name	WL120V LED12S/840 PSU WH
Full product code	871869606635599
Order code	06635599
Material Nr. (12NC)	910503910012
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696066355
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696066478

Dimensional drawing



CoreLine Wall-mounted

