



CoreLine Wall-mounted

WL120V LED12S/830 PSU WH

CoreLine Wall-mounted, 18 W, D344 mm, 1200 lm, 3000 K, IP65

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Wall-mounted range of LED products can be used to replace traditional wall-mounted luminaires incorporating compact fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

| General Information | | | |
|--------------------------|---|------------------------------------|---|
| Lamp family code | LED12S [LED module, system flux 1200 lm] | Flammability mark | For mounting on normally flammable surfaces |
| Light source replaceable | No | ENEC mark | - |
| Number of gear units | 1 unit | Glow-wire test | Temperature 850 °C, duration 30 s |
| Driver included | Yes | EU RoHS compliant | Yes |
| Remarks | * -Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. | Light Technical | |
| Lighting Technology | LED | Luminous Flux | 1,200 lm |
| Value ladder | Performance | Correlated Color Temperature (Nom) | 3000 K |
| CE mark | Yes | Luminous Efficacy (rated) (Nom) | 67 lm/W |
| Warranty period | 3 years + 2 years upon registration | Color rendering index (CRI) | >80 |
| | | Number of light sources | 1 |
| | | Beam angle of light source | 120 degree(s) |
| | | Light source color | 830 warm white |
| | | Optic type | Symmetrical |
| | | Luminaire light beam spread | 180° |

CoreLine Wall-mounted

| | |
|--|-----------------------------------|
| Operating and Electrical | |
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Inrush current | 22 A |
| Inrush time | 0.32 ms |
| Power Consumption | 18 W |
| Power Factor (Fraction) | 0.9 |
| Connection | Push-in connector and pull relief |
| Cable | - |
| Number of products on MCB of 16 A type B | 15 |

| | |
|---------------------------|---------------|
| Temperature | |
| Ambient temperature range | -20 to +35 °C |

| | |
|-------------------------------|----------------------------|
| Controls and Dimming | |
| Dimmable | No |
| Driver/power unit/transformer | Power supply unit (On/Off) |
| Constant light output | No |

| | |
|------------------------|---------------------|
| Mechanical and Housing | |
| Housing Material | Composite materials |
| Reflector material | - |
| Optic material | Polycarbonate |
| Optical cover material | Polycarbonate |
| Fixation material | Polyamide |
| Housing Color | White |
| Optical cover finish | Opal |
| Overall height | 120 mm |

| | |
|------------------|--------|
| Overall diameter | 344 mm |
|------------------|--------|


| | |
|------------------------------|--|
| Approval and Application | |
| Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK10 [20 J vandal-resistant] |
| Protection class IEC | Safety class I |

| | |
|-------------------------------------|---------------------|
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | (0.47, 0.42) SDCM<3 |
| Power consumption tolerance | +/-10% |

| | |
|------------------------------------|-------|
| Application Conditions | |
| Performance ambient temperature Tq | 25 °C |
| Suitable for random switching | No |

| | |
|---------------------------------|--------------------------|
| Product Data | |
| Order product name | WL120V LED12S/830 PSU WH |
| Full product name | WL120V LED12S/830 PSU WH |
| Full product code | 871869606641699 |
| Order code | 910503910018 |
| Material Nr. (12NC) | 910503910018 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718696066416 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 8718696066539 |

Dimensional drawing



CoreLine Wall-mounted

