



# CoreLine Recessed Spot

## RS140B LED6-32-/840 PSR PI6 ALU

LED Module 600 lm, 32 degree(s), 840 neutral white, Power supply unit regulating, Push-in connector 6-pole, Aluminium

CoreLine Recessed Spot is a recessed spot range designed to replace halogen-based luminaires. Its halogen-like look and attractive price make it easier for customers to make the switch to LED. This product provides a natural lighting effect for accent lighting applications, as well as instant energy savings and much longer lifetime – an environmentally friendly solution. With the push-in connectors, installation is fast and straightforward.

### Product data

General Information	
Lamp family code	LED6 [LED Module 600 lm]
Cap base	- [-]
Light source replaceable	No
Number of gear units	Unit
Driver included	Yes
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Lighting Technology	LED

Value ladder	Performance
CE mark	Yes
Warranty period	3 years + 2 years upon registration
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	-
Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	650 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	65 lm/W
Colour rendering index (CRI)	85
Beam angle of light source	32 degree(s)
Light source colour	840 neutral white

## CoreLine Recessed Spot

Optic type	Beam angle 32°
Optical cover type	Polycarbonate bowl/cover clear
Luminaire light beam spread	32°

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	7 A
Inrush time	500 ms
Power Consumption	10 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 6-pole
Cable	-
Number of products on MCB of 16 A type - B	

### Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating
Control interface	Analogue
Constant light output	No

### Mechanical and Housing

Housing material	Aluminium
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Stainless steel
Housing Colour	Aluminium
Optical cover/lens finish	Clear
Overall height	60 mm
Overall diameter	95 mm

### Approval and Application

Ingress protection code	IP54 [Dust accumulation-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L70


### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	Yes

### Product Data

Order product name	RS140B LED6-32-/840 PSR PI6 ALU
Full product name	RS140B LED6-32-/840 PSR PI6 ALU
Full EOC	871869606902899
Order code	06902899
Material no. (12 NC)	910503910057
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696069028
Numerator – packs per outer box	18
EAN/UPC - Case	8718696069141

## Dimensional drawing



## CoreLine Recessed Spot

