



# QVF LED

## BVP116 LED25/740 WB

LED Module 2500 lm, 740 neutral white, Wide beam

The QVF LED range of compact general-purpose floodlights are designed as an economical replacement for traditional halogen-lamp floodlights. The combination of high-power LEDs and a high-reflectivity optic ensures excellent light output for down- or uplighting applications. The floodlights' LED technology enables substantial energy and maintenance savings. A universal mounting bracket allows wall or surface mounting, with the possibility of tilting upwards or downwards. QVF LED floodlights can also be equipped with a combined presence/daylight sensor.

### Product data

General Information			
Lamp family code	LED25 [LED Module 2500 lm]	Standard tilt angle posttop	0°
Light source replaceable	No	Standard tilt angle side entry	0°
Number of gear units	1 unit	Correlated Color Temperature (Nom)	4000 K
Driver included	Yes	Luminous Efficacy (rated) (Nom)	70 lm/W
Light source engine type	LED	Color rendering index (CRI)	70
Lighting Technology	LED	Number of light sources	1
Embedded control	-	Light source color	740 neutral white
CE mark	Yes	Optical cover type	Glass
Warranty period	3 years	Luminaire light beam spread	100° x 120°
Flammability mark	-	Optic type outdoor	Wide beam
ENEC mark	-	Operating and Electrical	
Glow-wire test	Temperature 850 °C, duration 5 s	Input Voltage	220 to 240 V
EU RoHS compliant	Yes	Line Frequency	50 to 60 Hz
Light Technical		Inrush current	20 A
Upward light output ratio	0	Inrush time	100 ms
Luminous Flux	2,500 lm	Power Consumption	35 W
		Power Factor (Fraction)	0.9

## QVF LED

Connection	-
Cable	Cable 0.75 m without plug
Number of products on MCB of 16 A type B	-
<b>Temperature</b>	
Ambient temperature range	-20 to +40 °C
<b>Controls and Dimming</b>	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No
<b>Mechanical and Housing</b>	
Housing Material	Aluminum
Reflector material	Aluminum
Optic material	Aluminum
Optical cover material	Tempered glass
Fixation material	Steel
Housing Color	Aluminum
Mounting device	Wall-mounting bracket
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	225 mm
Overall width	187 mm
Overall height	128 mm
Effective projected area	0.05 m²
Dimensions (Height x Width x Depth)	128 x 187 x 225 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Surge Protection (Common/Differential)	4/4 kV
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.381, 0.381) SDCM< 5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.9 %
-------------------------------	-------

### Product Data

Order product name	BVP116 LED25/740 WB
Full product name	BVP116 LED25/740 WB
Full product code	871869606928899
Order code	06928899
Material Nr. (12NC)	910503910065
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696069288
Numerator - Packs per outer box	4
EAN/UPC - Case	8717943169733

## Dimensional drawing



