



# CoreLine SlimDownlight

## DN135B LED10S/840 PSU II WH

LED Module, system flux 1000 lm, 840 neutral white, Power supply unit (On/Off), Safety class II, White

CoreLine SlimDownlight is a range of ultra-thin recessed luminaires designed to replace downlight luminaires based on CFL-ni/CFL-I lamp technology. The product's attractive TCO makes it easy for customers to make the switch to LED. CoreLine SlimDownlight delivers a natural 'surface of light' effect for use in general lighting applications. It also offers instant energy savings and a much longer lifetime, making it a real value-for-money and environmentally friendly solution. Installation is easy, as the luminaire fits the same size of cut-out and has an extremely small build-in depth.

### Product data

General Information			
Lamp family code	LED10S [LED Module, system flux 1000 lm]	Service tag	Yes
Light source replaceable	No	Lighting Technology	LED
Number of gear units	1 unit	Value ladder	Performance
Gear	-	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Flammability mark	-
		ENEC mark	-
		Glow-wire test	Temperature 650 °C, duration 5 s
		EU RoHS compliant	Yes
		Light Technical	
		Luminous Flux	1,000 lm
		Correlated Color Temperature (Nom)	4000 K

## CoreLine SlimDownlight

Luminous Efficacy (rated) (Nom)	77 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Beam angle of light source	- degree(s)
Light source color	840 neutral white
Optic type	-
Optical cover type	Opal
Luminaire light beam spread	135°
Unified glare rating CEN	28

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	3.4 A
Inrush time	29 ms
Power Consumption	13 W
Power Factor (Fraction)	0.9
Connection	Push-in connector with 2 poles and pull relief
Cable	-
Number of products on MCB of 16 A type B	32

### Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum

Housing Color	White
Optical cover finish	Frosted
Overall height	20 mm
Overall diameter	165 mm

### Approval and Application

Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L70


### Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

### Product Data

Order product name	DN135B LED10S/840 PSU II WH
Full product name	DN135B LED10S/840 PSU II WH
Full product code	871869607043799
Order code	07043799
Material Nr. (12NC)	910503910111
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696070437
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696070512

## Dimensional drawing



## CoreLine SlimDownlight

