



# CoreLine SlimDownlight

## DN135B LED20S/830 PSU II WH

LED Module, system flux 2000 lm, 830 warm white, Power supply unit (On/Off), Safety class II, White

CoreLine slimdownlight delivers on the CoreLine promise of innovative, easy to use and high-quality indoor LED downlights. CoreLine slimdownlight is an innovative range of recessed and surface-mounted luminaires. It is designed to provide uniform lighting across multiple application areas. With instant energy savings and a longer lifetime, this is an environmentally friendly and cost saving solution. Its MultiColorTemp feature offers a choice of two color temperatures in a single luminaire. This makes it easy to select the right product, gives you the flexibility respond to customer preferences on site, and means fewer product codes on stock. Simple and easy installation means our slim downlight fits the same size cut-out, while the minimal built-in depth of 34mm makes this product an ideal space saving solution, especially for projects with limited fitting space. InterAct Ready option with integrated wireless communications in this family is available, to be used with InterAct gateways, sensors and software.

### Product data

General Information			
Lamp family code	LED20S [LED Module, system flux 2000 lm]	luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Light source replaceable	No		
Number of gear units	1 unit		
Gear	-		
Driver included	Yes		
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based	Service tag	Yes
		Lighting Technology	LED
		Glow-wire test	Temperature 650 °C, duration 5 s

# CoreLine SlimDownlight

Flammability mark	-
CE mark	Yes
ENEC mark	-
Warranty period	5 years
EU RoHS compliant	Yes
Value ladder	Performance

## Light Technical

Luminous Flux	2,000 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	71 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Beam angle of light source	- degree(s)
Light source color	830 warm white
Optic type	-
Optical cover type	Opal
Luminaire light beam spread	135°
Unified glare rating CEN	28

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
End CLO power consumption	- W
Inrush current	17 A
Inrush time	250 ms
Power Consumption	28 W
Power Factor (Fraction)	0.9
Connection	Push-in connector with 2 poles and pull relief
Cable	-
Number of products on MCB of 16 A type B	32

## Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

## Mechanical and Housing

Housing Material	Aluminum
------------------	----------

Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	White
Optical cover finish	Frosted
Overall height	20 mm
Overall diameter	215 mm

## Approval and Application

Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.42, 0.40) SDCM <5
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	5 %
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L70

## Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

## Product Data

Order product name	DN135B LED20S/830 PSU II WH
Full product name	DN135B LED20S/830 PSU II WH
Full product code	871869607044499
Order code	910503910112
Material Nr. (12NC)	910503910112
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696070444
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696070529

# CoreLine SlimDownlight

## Dimensional drawing

