



Cleanroom LED CR250B

CR250B LED35S/840 PSU W60L60 IP65

LED GreenLine 3500 lm, 840 neutral white, Power supply unit (On/Off), Dust penetration-protected, jet-proof

In applications where hygiene is crucially important, such as hospitals and food production facilities, customers want proven IP65- and IP54-rated luminaires that are safe to use and are an economical investment. This family of fixtures represents an affordable solution: the Philips LED engine delivers reliable, high-quality light, and the flexible mounting possibilities mean that this family can be used in a wide range of applications. The fixtures are also compliant with all relevant standards (CE, EMC, RoHS).

Product data

General Information		Value ladder	
Lamp family code	GRN35 [LED GreenLine 3500 lm]	CE mark	Performance
Light source replaceable	Yes	Warranty period	Yes
Number of gear units	Unit	Flammability mark	5 years
Driver included	Yes	ENEC mark	For mounting on easily flammable surfaces
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test	-
Lighting Technology	LED	EU RoHS compliant	Temperature 850 °C, duration 30 s
		Light Technical	
		Luminous Flux	Yes
		Correlated Colour Temperature	5 years
		Luminous efficacy (rated) (nom.)	For mounting on easily flammable surfaces
		Colour rendering index (CRI)	-
		Number of light sources	Temperature 850 °C, duration 30 s

Cleanroom LED CR250B

Light source colour	840 neutral white
Optic type	-
Optical cover type	Clear glass with diffuser foil
Luminaire light beam spread	110°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	13 A
Inrush time	270 ms
Power Consumption	40 W
Power Factor (Fraction)	0.9
Connection	Screw connector
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------


Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing material	Steel
Reflector material	-
Optic material	Polystyrene
Optical cover/lens material	Tempered glass
Fixation material	Stainless steel
Housing Colour	White
Optical cover/lens finish	Opal
Overall length	595 mm
Overall width	595 mm
Overall height	135 mm

Dimensional drawing



Dimensions (height x width x depth)	135 x 595 x 595 mm
-------------------------------------	--------------------

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Sustainability rating	-
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-5%
Initial chromaticity	(0.38, 0.38) SDCM <4
Power consumption tolerance	+/-5%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* L90	50,000 h
Lumen maintenance at median useful life* L80	100,000 h

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

Product Data

Order product name	CR250B LED35S/840 PSU W60L60 IP65
Full product name	CR250B LED35S/840 PSU W60L60 IP65
Full EOC	871869607283700
Order code	07283700
Material no. (12 NC)	910503910167
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696072837
Numerator – packs per outer box	1
EAN/UPC – Case	8718696072837

Cleanroom LED CR250B

