



# Ledinaire SlimDownlight

## DN065B LED10S/830 PSU II WH

Ledinaire SlimDownlight, 11 W, 950 lm, 3000 K, Frosted, IP20

The LEDINAIRE range contains a selection of popular off-the-shelf LED luminaires that come with the high Philips quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need

### Product data

General Information		Connection	
Light source replaceable	No	Screw connector	
Lighting Technology	LED	Temperature	
Warranty period	3 years	Ambient temperature range	0 to +35 °C
Value ladder	Value	Controls and Dimming	
Light Technical		Dimmable	No
Luminous Flux	950 lm	Driver/power unit/transformer	Power supply unit (On/Off)
Correlated Color Temperature (Nom)	3000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	86 lm/W	Housing Material	Plastic
Color rendering index (CRI)	>80	Reflector material	Polycarbonate
Light source color	830 warm white	Optic material	Polycarbonate
Luminaire light beam spread	90° x 90°	Fixation material	Stainless steel
Operating and Electrical		Housing Color	White
Line Frequency	50 or 60 Hz	Optical cover finish	Frosted
Input Frequency	50 or 60 Hz	Overall length	30 mm
Power Consumption	11 W	Overall width	30 mm
Power Factor (Fraction)	0.8	Overall height	30 mm

## Ledinaire SlimDownlight

Overall diameter	175 mm
Dimensions (Height x Width x Depth)	30 x 30 x 30 mm
<b>Approval and Application</b>	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
<b>Initial Performance (IEC Compliant)</b>	
Initial chromaticity	(0.42, 0.40) SDCM <5
Power consumption tolerance	+/-10%

<b>Product Data</b>	
Order product name	DN065B LED10S/830 PSU II WH
Full product name	DN065B LED10S/830 PSU II WH
Full product code	871869938175299
Order code	910503910331
Material Nr. (12NC)	910503910331
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699381752
Numerator - Packs per outer box	12
EAN/UPC - Case	8718699381790

### Dimensional drawing

