



# Ledinaire SlimDownlight

## DN065B LED10S/840 PSU II WH

Ledinaire SlimDownlight, 11 W, 1000 lm, 4000 K, Frosted, IP20

The LEDINAIRE range contains a selection of popular off-the-shelf LED luminaires that come with the high Philips quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need

### Product data

|                                    |                   |                               |  |
|------------------------------------|-------------------|-------------------------------|--|
| <b>General Information</b>         |                   | <b>Connection</b>             |  |
| Light source replaceable           | No                | Screw connector               |  |
| Lighting Technology                | LED               | <b>Temperature</b>            |  |
| Warranty period                    | 3 years           | Ambient temperature range     |  |
| Value ladder                       | Value             | 0 to +35 °C                   |  |
| <b>Light Technical</b>             |                   | <b>Controls and Dimming</b>   |  |
| Luminous Flux                      | 1,000 lm          | Dimmable                      |  |
| Correlated Color Temperature (Nom) | 4000 K            | No                            |  |
| Luminous Efficacy (rated) (Nom)    | 91 lm/W           | Driver/power unit/transformer |  |
| Color rendering index (CRI)        | >80               | Power supply unit (On/Off)    |  |
| Light source color                 | 840 neutral white | <b>Mechanical and Housing</b> |  |
| Luminaire light beam spread        | 90° x 90°         | Housing Material              |  |
| <b>Operating and Electrical</b>    |                   | Plastic                       |  |
| Line Frequency                     | 50 or 60 Hz       | Reflector material            |  |
| Input Frequency                    | 50 or 60 Hz       | Polycarbonate                 |  |
| Power Consumption                  | 11 W              | Optic material                |  |
| Power Factor (Fraction)            | 0.8               | Polycarbonate                 |  |
|                                    |                   | Fixation material             |  |
|                                    |                   | Stainless steel               |  |
|                                    |                   | Housing Color                 |  |
|                                    |                   | White                         |  |
|                                    |                   | Optical cover finish          |  |
|                                    |                   | Frosted                       |  |
|                                    |                   | Overall length                |  |
|                                    |                   | 30 mm                         |  |
|                                    |                   | Overall width                 |  |
|                                    |                   | 30 mm                         |  |
|                                    |                   | Overall height                |  |
|                                    |                   | 30 mm                         |  |

Ledinaire SlimDownlight

|                                     |                         |
|-------------------------------------|-------------------------|
| Overall diameter                    | 175 mm                  |
| Dimensions (Height x Width x Depth) | 30 x 30 x 30 mm         |
| Approval and Application            |                         |
| Ingress protection code             | IP20 [Finger-protected] |
| Mech. impact protection code        | IK02 [0.2 J standard]   |
| Protection class IEC                | Safety class II         |
| Initial Performance (IEC Compliant) |                         |
| Initial chromaticity                | (0.38, 0.38) SDCM <5    |
| Power consumption tolerance         | +/-10%                  |

|                                 |                             |
|---------------------------------|-----------------------------|
| Product Data                    |                             |
| Order product name              | DN065B LED10S/840 PSU II WH |
| Full product name               | DN065B LED10S/840 PSU II WH |
| Full product code               | 871869938176999             |
| Order code                      | 910503910332                |
| Material Nr. (12NC)             | 910503910332                |
| Numerator - Quantity Per Pack   | 1                           |
| EAN/UPC - Product/Case          | 8718699381769               |
| Numerator - Packs per outer box | 12                          |
| EAN/UPC - Case                  | 8718699381806               |

Dimensional drawing

