



Ledinaire SlimDownlight

DN065B LED20S/840 PSU II WH

Ledinaire SlimDownlight, 23 W, 2000 lm, 4000 K, Frosted, IP20

The LEDINAIRE range contains a selection of popular off-the-shelf LED luminaires that come with the high Philips quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need

Product data

General Information	
Light source replaceable	No
Lighting Technology	LED
Value ladder	Value
Warranty period	3 years
Light Technical	
Luminous Flux	2,000 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	87 lm/W
Colour rendering index (CRI)	>80
Light source colour	840 neutral white
Luminaire light beam spread	90° x 90°
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input frequency	50 or 60 Hz
Power Consumption	23 W
Power Factor (Fraction)	0.8

Connection	Screw connector
Temperature	
Ambient temperature range	0 to +35 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Mechanical and Housing	
Housing material	Plastic
Reflector material	Polycarbonate
Optic material	Polycarbonate
Fixation material	Stainless steel
Housing Colour	White
Optical cover/lens finish	Frosted
Overall length	30 mm
Overall width	30 mm
Overall height	30 mm

Ledinaire SlimDownlight

Overall diameter	225 mm
Dimensions (height x width x depth)	30 x 30 x 30 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%

Product Data	
Order product name	DN065B LED20S/840 PSU II WH
Full product name	DN065B LED20S/840 PSU II WH
Full EOC	871869938178399
Order code	38178399
Material no. (12 NC)	910503910334
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699381783
Numerator – packs per outer box	12
EAN/UPC – Case	8718699381820

Dimensional drawing

