



# SmartForm LED BCS460

## BCS460 LED24/840 PSD W22L124 MLO-PC

SmartForm surface mnt BCS460, LED Module 2400 lm, 840 neutral white, Power supply unit with DALI interface, Micro-lens optic in polycarbonate cover

We all feel and perform better in a pleasant, comfortable working environment. Designed for use in offices, shops and schools, the SmartForm family of surface-mounted luminaires combines best-in-class lighting with a clean, distinctive design. These ultra-flat luminaires are available with a choice of MASTER TL5, TL5 ECO or LED light sources in rectangular and square versions. They can also be used to form light-lines and structures. With its wide choice of very efficient and comfortable micro-optics and covers, SmartForm surface-mounted provides the ideal solution for every situation. Lighting controls can be added for further energy saving.


### Product data

General Information			
Lamp family code	LED24 [LED Module 2400 lm]		useful life (B50) value also represents the B10 value.
Cap base	- [-]	Product family code	BCS460 [SmartForm surface mnt BCS460]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	Unit	Embedded control	-
Driver included	Yes	CE mark	Yes
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median	Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s

# SmartForm LED BCS460

EU RoHS compliant	Yes
<b>Light Technical</b>	
Luminous Flux	2,000 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	93 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	- degree(s)
Light source colour	840 neutral white
Optic type	-
Optical cover type	Micro-lens optic in polycarbonate cover
Luminaire light beam spread	120°
Unified Glare Rating (CEN)	Not applicable
<b>Operating and Electrical</b>	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	48 A
Inrush time	1 ms
Power Consumption	21.5 W
Power Factor (Fraction)	0.95
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	20
<b>Temperature</b>	
Ambient temperature range	+10 to +40 °C
<b>Controls and Dimming</b>	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
<b>Mechanical and Housing</b>	
Housing material	Steel
Reflector material	-

## Dimensional drawing



Optic material	-
Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Textured
Overall length	1,240 mm
Overall width	217 mm
Overall height	56 mm
Dimensions (height x width x depth)	56 x 217 x 1240 mm
Parts colour	-
<b>Approval and Application</b>	
Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%
<b>Application Conditions</b>	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No
<b>Product Data</b>	
Order product name	BCS460 LED24/840 PSD W22L124 MLO-PC
Full product name	BCS460 LED24/840 PSD W22L124 MLO-PC
Full EOC	871794391549100
Order code	91549100
Material no. (12 NC)	910504077503
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8717943915491
Numerator – packs per outer box	1
EAN/UPC – Case	8717943915491

## SmartForm LED BCS460

