



SmartForm LED BPS460

BPS460 LED24/840 PSD W16L124 LIN-PC SMT1

SmartForm suspended BPS460, LED Module 2400 lm, 840 neutral white, Power supply unit with DALI interface, Linear-lens array in polycarbonate cover

We all feel and perform better in a pleasant, comfortable working environment. Designed for use in offices, shops and schools, the SmartForm family of suspended luminaires combines best-in-class lighting with a clean, distinctive design. These ultra-flat luminaires are available with a choice of MASTER TL5, TL5 ECO or LED light sources in rectangular and square versions with direct/indirect lighting combinations. They can also be used to form light-lines and structures. With its wide choice of very efficient and comfortable micro-optics and covers, SmartForm suspended provides the ideal solution for every situation. Lighting controls can be added for further energy saving.

Product data

General Information			
Lamp family code	LED24 [LED Module 2400 lm]		useful life (B50) value also represents the B10 value.
Light source replaceable	No	Product family code	BPS460 [SmartForm suspended BPS460]
Number of gear units	Unit	Lighting Technology	LED
Driver included	Yes	Embedded control	-
Remarks	* - According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median	CE mark	Yes
		Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s

SmartForm LED BPS460

EU RoHS compliant	Yes
-------------------	-----

Light Technical

Luminous Flux	2,200 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	102 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	- degree(s)
Light source colour	840 neutral white
Optic type	-
Optical cover type	Linear-lens array in polycarbonate cover
Luminaire light beam spread	140°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	48 A
Inrush time	1 ms
Power Consumption	21.5 W
Power Factor (Fraction)	0.95
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	20

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing material	Steel
Reflector material	-
Optic material	-

Optical cover/lens material	Polycarbonate
Fixation material	Stainless steel
Housing Colour	White
Optical cover/lens finish	Textured
Overall length	1,240 mm
Overall width	157 mm
Overall height	56 mm
Dimensions (height x width x depth)	56 x 157 x 1240 mm
Parts colour	-

Approval and Application

Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No

Product Data

Order product name	BPS460 LED24/840 PSD W16L124 LIN-PC SMT1
Full product name	BPS460 LED24/840 PSD W16L124 LIN-PC SMT1
Full EOC	871794391553800
Order code	91553800
Material no. (12 NC)	910504077903
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8717943915538
Numerator – packs per outer box	1
EAN/UPC - Case	8717943915538

SmartForm LED BPS460

Dimensional drawing

