



# LumiStone

## SP520P/SP522P/ SP524P/SP526P

### SP522P 2xLED20S/840 PSD-E SMTT WH

Dual mod. Suspension set D/I, 2, LED Module, system flux 2000 lm, 840 neutral white, Power supply unit with DALI interface external, White

Customers within the office, retail and hospitality sectors want to create spaces with a pleasant and inviting atmosphere. Luminaires with an appealing design and top-notch performance play a pivotal role in achieving this. LumiStone is a LED luminaire consisting of two smaller ellipses rather than the traditional single voluminous piece. The ellipses have soft curvatures and resemble smooth stones found in nature. The flexible light effects created with direct and indirect light make LumiStone the perfect choice for inspiring lighting designs. Thanks to its cutting-edge LED technology, LumiStone is also highly energy-efficient, delivering immediate savings on operational costs. A range of innovative mounting options make LumiStone extremely versatile in application.

#### Product data

General Information		Remarks
Lamp family code	LED20S [LED Module, system flux 2000 lm]	
Cap-Base	- [-]	
Light source replaceable	No	
Number of gear units	1 unit	
Driver included	Yes	
		*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.

## LumiStone SP520P/SP522P/SP524P/SP526P

Product family code	SP522P [Dual mod. Suspension set D/I]
Lighting Technology	LED
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC plus mark
Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	Yes

### Light Technical

Luminous Flux	4,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	143 lm/W
Color rendering index (CRI)	≥80
Number of light sources	2
Beam angle of light source	- degree(s)
Light source color	840 neutral white
Optic type	-
Luminaire light beam spread	124°
Unified glare rating CEN	Not applicable

### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	48 A
Inrush time	0.180 ms
Power Consumption	28 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	Cable 2.1 m without plug
Number of products on MCB of 16 A type B	20

### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface external
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Polycarbonate
Optic material	-
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	White
Optical cover finish	Matte
Overall length	1,510 mm
Overall width	334 mm
Overall height	75 mm
Dimensions (Height x Width x Depth)	75 x 334 x 1510 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

### Product Data

Order product name	SP522P 2xLED20S/840 PSD-E SMTT WH
Full product name	SP522P 2xLED20S/840 PSD-E SMTT WH
Full product code	871794391846100
Order code	91846100
Material Nr. (12NC)	910504080203
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943918461
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943918461

## LumiStone SP520P/SP522P/SP524P/SP526P

### Dimensional drawing

