



# SmartBalance, suspended

## SP482P LED40S/830 PSD ACC-MLO SM1

SmartBalance Suspended Mounted, LED module, system flux 4000 lm, 830 warm white, Power supply unit with DALI interface, Acrylate micro-lens optic clear

Although in many cases the functional lighting performance is key, customers are also keen to apply luminaires that are attractive and/or unobtrusive. Especially in applications where luminaires need to be surface-mounted or suspended, it can be difficult to satisfy both these requirements. SmartBalance is clearly the next step in surface-mounted and suspended luminaires for the specification market. It not only offers increased energy efficiency, but is also visually appealing without being intrusive. And its design helps to minimize clutter on the ceiling and meets all relevant office norms. SmartBalance is also available in recessed and free floor-standing versions.

### Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that The environment in which The luminaire is to be installed is suitably checked
- If The above advice is not taken and The luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

### Product data

General Information			
Lamp family code	LED40S [LED module, system flux 4000 lm]	Gear	-
Cap-Base	- [-]	Driver included	Yes
Light source replaceable	No	Remarks	*.-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there
Number of gear units	1 unit		

## SmartBalance, suspended

	is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Service tag	Yes
Product family code	SP482P [SmartBalance Suspended Mounted]
Lighting Technology	LED
Value ladder	Specification
Embedded control	-
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC plus mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

### Light Technical

Luminous Flux	4,100 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	116 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Beam angle of light source	- degree(s)
Light source color	830 warm white
Optic type	-
Optical cover type	Acrylate micro-lens optic clear
Luminaire light beam spread	100°
Unified glare rating CEN	16

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	48 A
Inrush time	0.180 ms
Power Consumption	35 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	Cable 1.7 m without plug 5-pole white
Number of products on MCB of 16 A type B	20

### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI

Constant light output	No
-----------------------	----

### Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	-
Optic material	-
Optical cover material	Acrylate
Fixation material	Steel
Housing Color	White
Optical cover finish	Textured
Overall length	1,340 mm
Overall width	240 mm
Overall height	50 mm
Dimensions (Height x Width x Depth)	50 x 240 x 1340 mm

### Approval and Application

Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L85

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No

### Product Data

Order product name	SP482P LED40S/830 PSD ACC-MLO SM1
Full product name	SP482P LED40S/830 PSD ACC-MLO SM1
Full product code	871829126798000
Order code	910504087703
Material Nr. (12NC)	910504087703
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291267980
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291267980

## SmartBalance, suspended

### Dimensional drawing

