



SmartBalance Wall-mounted

WL484W LED52S/830 PSD D/I SW WH

SmartBalance wall-mounted, LED Module, system flux 5200 lm, 830 warm white, Power supply unit with DALI interface, White

Striking the right balance between the different lighting needs in a patient room is a challenge for many hospitals. That's why our bed-head luminaires offer some of the key functionalities required by both patients and staff. The SmartBalance, wall-mounted luminaire combines high-quality lighting performance with a stylish, timeless design. General ambience light is provided indirectly via the upper part of the luminaire. The lower part delivers direct, diffuse light, allowing patients to read and clinical staff to carry out examinations at the bed.

Product data

General Information			
Lamp family code	LED52S [LED Module, system flux 5200 lm]		useful life (B50) value also represents the B10 value.
Cap base	- [-]	Product family code	WL484W [SmartBalance wall-mounted]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	2 units	Embedded control	-
Gear	-	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median		
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC plus mark
		Glow-wire test	Temperature 650 °C, duration 5 s
		EU RoHS compliant	Yes
Light Technical			
Luminous Flux	5,200 lm		

SmartBalance Wall-mounted

Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	116 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	- degree(s)
Light source colour	830 warm white
Optic type	-
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	156°

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	48 A
Inrush time	0.18 ms
Power Consumption	45 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	20

Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing material	Aluminium
Reflector material	Aluminium
Optic material	-
Optical cover/lens material	Polycarbonate

Fixation material	Stainless steel
Housing Colour	White
Optical cover/lens finish	Textured
Overall length	900 mm
Overall width	152 mm
Overall height	52 mm
Dimensions (height x width x depth)	52 x 152 x 900 mm

Approval and Application

Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%


Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No

Product Data

Order product name	WL484W LED52S/830 PSD D/I SW WH
Full product name	WL484W LED52S/830 PSD D/I SW WH
Full EOC	871794310527400
Order code	10527400
Material no. (12 NC)	910504094103
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8717943105274
Numerator – packs per outer box	1
EAN/UPC - Case	8717943105274

Dimensional drawing



SmartBalance Wall-mounted

