



# SmartBalance Wall-mounted

## WL484W LED40S/830 PSD D/I SW WH

SmartBalance wall-mounted, LED module, system flux 4000 lm, 830 warm white, Power supply unit with DALI interface, White

Striking the right balance between the different lighting needs in a patient room is a challenge for many hospitals. That's why our bed-head luminaires offer some of the key functionalities required by both patients and staff. The SmartBalance, wall-mounted luminaire combines high-quality lighting performance with a stylish, timeless design. General ambience light is provided indirectly via the upper part of the luminaire. The lower part delivers direct, diffuse light, allowing patients to read and clinical staff to carry out examinations at the bed.

### Product data

General Information		Product family code	
Lamp family code	LED40S [LED module, system flux 4000 lm]	Product family code	WL484W [SmartBalance wall-mounted]
Cap-Base	- [-]	Lighting Technology	LED
Light source replaceable	No	Embedded control	-
Number of gear units	2 units	CE mark	Yes
Gear	-	Warranty period	5 years
Driver included	Yes	Flammability mark	For mounting on normally flammable surfaces
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	ENEC mark	ENEC plus mark
		Glow-wire test	Temperature 650 °C, duration 5 s
		EU RoHS compliant	Yes
		Light Technical	
		Luminous Flux	4,000 lm
		Correlated Color Temperature (Nom)	3000 K
		Luminous Efficacy (rated) (Nom)	116 lm/W

SmartBalance Wall-mounted

Color rendering index (CRI)	≥80
Number of light sources	1
Beam angle of light source	- degree(s)
Light source color	830 warm white
Optic type	-
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	156°

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	48 A
Inrush time	0.18 ms
Power Consumption	34.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	20

Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Aluminum
Optic material	-
Optical cover material	Polycarbonate
Fixation material	Stainless steel

Housing Color	White
Optical cover finish	Textured
Overall length	900 mm
Overall width	152 mm
Overall height	52 mm
Dimensions (Height x Width x Depth)	52 x 152 x 900 mm

Approval and Application

Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%


Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No

Product Data

Order product name	WL484W LED40S/830 PSD D/I SW WH
Full product name	WL484W LED40S/830 PSD D/I SW WH
Full product code	871869686901700
Order code	910504096203
Material Nr. (12NC)	910504096203
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696869017
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696869017

Dimensional drawing



## SmartBalance Wall-mounted

