



# TrueLine, surface mounted

## SM530C LED43S/830 PSD PI5 L1410 ALU

TrueLine OC, LED module, system flux 4300 lm, 830 warm white, Power supply unit with DALI interface, Push-in connector 5-pole, Aluminium

Architects need a lighting solution that matches the interior architecture of the property they are working on. They want a light line with an elegant design and very high light levels. Specifiers need luminaires that enable them to save energy while at the same time providing the right level of light, in compliance with office lighting norms. And office workers want visually comfortable lighting conditions that help them perform better. TrueLine Recessed is able to meet all of these different requirements. TrueLine is also available in recessed and suspended versions.

### Warnings and Safety

- The product is IP40 and as such is not protected against water ingress, so we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe use and the product warranty will become void

### Product data

General Information		Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median
Lamp family code	LED43S [LED module, system flux 4300 lm]		
Cap base	- [-]		
Light source replaceable	No		
Number of gear units	Unit		
Gear	-		
Driver included	Yes		

## TrueLine, surface mounted

	useful life (B50) value also represents the B10 value.
Product family code	SM530C [TrueLine OC]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC plus mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

### Light Technical

Luminous Flux	4,300 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	126 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	- degree(s)
Light source colour	830 warm white
Optic type	-
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	100°
Unified Glare Rating (CEN)	19

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	19 A
Inrush time	0.28 ms
Power Consumption	34 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	24

### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing material	Aluminium
Reflector material	-
Optic material	-
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Steel
Housing Colour	Aluminium
Optical cover/lens finish	Frosted
Overall length	1,409 mm
Overall width	55 mm
Overall height	93 mm
Dimensions (height x width x depth)	93 x 55 x 1409 mm

### Approval and Application

Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L85

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No

### Product Data

Order product name	SM530C LED43S/830 PSD P15 L1410 ALU
Full product name	SM530C LED43S/830 PSD P15 L1410 ALU
Full EOC	871869687421900
Order code	87421900
Material no. (12 NC)	910504099403
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8718696874219
Numerator – packs per outer box	1
EAN/UPC – Case	8718696874219

## TrueLine, surface mounted

### Dimensional drawing

