



# TrueLine, suspended

## SP532P LED36S/840 POE ACL SW2 L1170 ALU

TrueLine DIRECT/INDIRECT OC, LED module, system flux 3600 lm, 840 neutral white, Luminaire controller with power over Ethernet, ActiLume, Aluminum

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine surface is rated  $UGR < 19$ , which is compliant with all office norms (OC). TrueLine also comes in surface and recess-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 140 lm/W and the option to upgrade to wireless connectivity and control.

### Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

### Product data

General Information			
Lamp family code	LED36S [LED module, system flux 3600 lm]	Light source replaceable	No
Cap-Base	- [-]	Number of gear units	1 unit
		Gear	GRT [Gear tray (without gear)]

## TrueLine, suspended

Driver included	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Service tag	Yes
Product family code	SP532P [TrueLine DIRECT/INDIRECT OC]
Lighting Technology	LED
Value ladder	Specification
Embedded control	ActiLume
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC plus mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

### Light Technical

Luminous Flux	3,600 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	138 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Light source color	840 neutral white
Optic type	-
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	100°
Unified glare rating CEN	16

### Operating and Electrical

Input Voltage	51 to 54 V
Line Frequency	- Hz
End CLO power consumption	- W
Inrush current	19 A
Inrush time	0.28 ms
Power Consumption	26 W
Connection	RJ45 connector, male
Cable	-
Number of products on MCB of 16 A type B	-

### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Luminaire controller with power over Ethernet

Control interface	Power over Ethernet
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	-
Optical cover material	Polymethyl methacrylate
Fixation material	Stainless steel
Housing Color	Aluminum
Optical cover finish	Frosted
Overall length	1,170 mm
Overall width	55 mm
Overall height	121 mm
Dimensions (Height x Width x Depth)	121 x 55 x 1170 mm

### Approval and Application

Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class III

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L85

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

### Product Data

Order product name	SP532P LED36S/840 POE ACL SW2 L1170 ALU
Full product name	SP532P LED36S/840 POE ACL SW2 L1170 ALU
Full product code	871869687498100
Order code	910504101703
Material Nr. (12NC)	910504101703
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696874981
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696874981

## TrueLine, suspended

### Dimensional drawing

