



# PowerBalance, surface mounted

## SM461V LED34S/840 POE W17L169 ACL

PowerBalance Surface-mounted, LED module, system flux 3400 lm, 840 neutral white, Luminaire controller with power over Ethernet, ActiLume

When it comes to lighting an office space with LED luminaires, people are usually willing to invest in sustainability provided the investment pays back. At the same time, the system should comply with office lighting norms to ensure a comfortable working environment. PowerBalance is Philips' most energy-efficient office-norm-compliant LED luminaire. It more than halves energy costs compared to a T5 solution, and the light source has a longer lifetime. This results in significantly lower operational costs, ensuring a payback that meets the needs of the specification market. PowerBalance surface-mounted luminaires are easy to install on ceilings thanks to their intuitive mounting system. PowerBalance is also available in a recessed version.

### Product data

General Information			
Lamp family code	LED34S [LED module, system flux 3400 lm]		maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Cap-Base	- [-]	Product family code	SM461V [PowerBalance Surface-mounted]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	1 unit	Glow-wire test	Temperature 850 °C, duration 5 s
Driver included	Yes	Flammability mark	For mounting on normally flammable surfaces
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen	CE mark	Yes
		ENEC mark	ENEC plus mark
		Warranty period	5 years

## PowerBalance, surface mounted

EU RoHS compliant	Yes
Embedded control	ActiLume

### Light Technical

Luminous Flux	3,400 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	133 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Beam angle of light source	- degree(s)
Light source color	840 neutral white
Optic type	-
Luminaire light beam spread	120°
Unified glare rating CEN	19

### Operating and Electrical

Input Voltage	51 to 54 V
Line Frequency	- Hz
Inrush current	48 A
Inrush time	1 ms
Power Consumption	25.5 W
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	20

### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Luminaire controller with power over Ethernet
Control interface	Power over Ethernet Plus
Constant light output	No

### Mechanical and Housing

Housing Material	Steel
Reflector material	Polycarbonate

Optic material	-
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Matte
Overall length	1,685 mm
Overall width	171 mm
Overall height	85 mm
Dimensions (Height x Width x Depth)	85 x 171 x 1685 mm

### Approval and Application

Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class III

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

### Product Data

Order product name	SM461V LED34S/840 POE W17L169 ACL
Full product name	SM461V LED34S/840 POE W17L169 ACL
Full product code	871869906493800
Order code	910504109403
Material Nr. (12NC)	910504109403
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699064938
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699064938

## Dimensional drawing

## PowerBalance, surface mounted

