



TrueLine, surface mounted

SM534C LED40S/840 PSD PI5 L1130 ALU

TrueLine Surface Mounted Asym - LED Module, system flux 4000 lm - 840 neutral white - Power supply unit with DALI interface - - - Push-in connector 5-pole - 1130 mm - Aluminum - -

Architects need a lighting solution that matches the interior architecture of the property they are working on. They want a light line with an elegant design and very high light levels. Specifiers need luminaires that enable them to save energy while at the same time providing the right level of light, in compliance with office lighting norms. And office workers want visually comfortable lighting conditions that help them perform better. TrueLine Recessed is able to meet all these different requirements. TrueLine is also available in recessed and suspended versions.

Product data

General Information			
Number of light sources	1 pc	Optic type	-
Lamp family code	LED40S [LED Module, system flux 4000 lm]	Optical cover/lens type	Polymethyl methacrylate bowl/cover
Beam angle of light source	- °	Luminaire light beam spread	90°
Light source color	840 neutral white	Embedded control	-
Cap-Base	- [-]	Control interface	DALI
Light source replaceable	No	Connection	Push-in connector 5-pole
Number of gear units	1 unit	Cable	-
Gear	-	Protection class IEC	Safety class I
Driver/power unit/transformer	Power supply unit with DALI interface	Standard RAL color	-
Driver included	Yes	Glow-wire test	Temperature 650 °C, duration 5 s

TrueLine, surface mounted

Flammability mark	For mounting on normally flammable surfaces
Type description	Office compliant version
CE mark	CE mark
ENEC mark	ENEC plus mark
UL mark	-
Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB of 16 A type B	24
RoHS mark	RoHS mark
Accessory PFC	N/A
Product family code	SM534C [TrueLine Surface Mounted Asym]
Unified glare rating CEN	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Control signal voltage	0-16 V DC DALI
End CLO power consumption	- W
Inrush current	19 A
Inrush time	0.28 ms
Power Factor (Min)	0.9

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Geometry	-
Housing Material	Aluminum
Reflector material	-
Optic material	-
Optical cover/lens material	Polymethyl methacrylate
Gear tray material	Steel
Fixation material	Steel
Optical cover/lens finish	Frosted
Overall length	1130 mm

Overall width	55 mm
Overall height	93 mm
Length	1130 mm
Color	Aluminum

Approval and Application

Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	4000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	116 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	≥80
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	34.5 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L85

Application Conditions


Ambient temperature range	+10 to +40 °C
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No

Product Data

Full product code	871869907206300
Order product name	SM534C LED40S/840 PSD P15 L1130 ALU
EAN/UPC - Product	8718699072063
Order code	910504112603
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910504112603
Net Weight (Piece)	3.300 kg

TrueLine, surface mounted

Dimensional drawing



TrueLine surface-mounted SM530C-SM534C

