



Iridium LED Mini

BGS451 ECO43--2S/740 I MSO GR CLO

Mini Iridium LED, LED EconomyLine 4300 lm, 740 neutral white, Safety class I, Medium wide street optic, Grey, Constant light output

The second generation of compact Mini Iridium LED road-lighting luminaires offers a much wider scope of application thanks to a more powerful LED engine and brand new optics, which allow maximum energy savings in residential streets. Additional control devices can be fitted into the mast and communicate with the luminaire to further increase energy savings. This new generation of Mini Iridium LED also gives municipal authorities the freedom to change the atmosphere of the street thanks to the choice of different color temperatures (warm, neutral and cool white).

Product data

General Information			
Lamp family code	ECO43 [LED EconomyLine 4300 lm]	Glow-wire test	Temperature 650 °C, duration 5 s
Light source replaceable	Yes	Flammability mark	-
Number of gear units	1 unit	CE mark	Yes
Driver included	Yes	ENEC mark	ENEC mark
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Warranty period	5 years
		EU RoHS compliant	Yes
		Embedded control	Constant light output
		Light Technical	
Light source engine type	LED	Upward light output ratio	0.03
Product family code	BGS451 [Mini Iridium LED]	Luminous Flux	4,321 lm
Lighting Technology	LED	Standard tilt angle posttop	10°
		Standard tilt angle side entry	0°
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	122 lm/W

Iridium LED Mini

Color rendering index (CRI)	70
Number of light sources	1
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	180°
Optic type outdoor	Medium wide street optic

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	28.2 W
Average CLO power consumption	31.7 W
End CLO power consumption	35.2 W
Inrush current	22 A
Inrush time	0.29 ms
Power Consumption	35.2 W
Power Factor (Fraction)	0.95
Connection	Internal connector
Cable	-
Number of products on MCB of 16 A type B	20

Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating with constant light output
Constant light output	Yes

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Post-top for diameter 60 to 76 mm
Optical cover shape	Convex lens
Optical cover finish	Clear

Overall length	529 mm
Overall width	265 mm
Overall height	154.5 mm
Effective projected area	0.032 m²
Dimensions (Height x Width x Depth)	155 x 265 x 529 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.37) SDCM<5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 75000 h	7.5 %
Lumen maintenance at median useful life* 75000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Order product name	BGS451 ECO43--2S/740 I MSO GR CLO
Full product name	BGS451 ECO43--2S/740 I MSO GR CLO
Full product code	871794385075400
Order code	910504999218
Material Nr. (12NC)	910504999218
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943850754
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943850754

Iridium LED Mini

Dimensional drawing

