



Iridium LED Mini

BGS451 ECO43--2S/740 II MSO GR MSP CLO-L

Mini Iridium LED, LED EconomyLine 4300 lm, 740 neutral white, Safety class II, Medium wide street optic, Grey, Marine salt protected coating, Constant light output and LumiStep dimming 8 hours

The second generation of compact Mini Iridium LED road-lighting luminaires offers a much wider scope of application thanks to a more powerful LED engine and brand new optics, which allow maximum energy savings in residential streets. Additional control devices can be fitted into the mast and communicate with the luminaire to further increase energy savings. This new generation of Mini Iridium LED also gives municipal authorities the freedom to change the atmosphere of the street thanks to the choice of different color temperatures (warm, neutral and cool white).

Product data

General Information			
Lamp family code	ECO43 [LED EconomyLine 4300 lm]	Product family code	BGS451 [Mini Iridium LED]
Light source replaceable	Yes	Lighting Technology	LED
Number of gear units	1 unit	Glow-wire test	Temperature 650 °C, duration 5 s
Driver included	Yes	Flammability mark	-
Photocell	-	CE mark	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	ENEC mark	ENEC mark
Light source engine type	LED	Warranty period	5 years
		EU RoHS compliant	Yes
		Embedded control	Constant light output and LumiStep dimming 8 hours
		Light Technical	
		Upward light output ratio	0.03
		Luminous Flux	4,321 lm

Iridium LED Mini

Standard tilt angle posttop	10°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	122 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	180°
Optic type outdoor	Medium wide street optic

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	28.2 W
Average CLO power consumption	31.7 W
End CLO power consumption	35.2 W
Inrush current	22 A
Inrush time	0.29 ms
Power Consumption	35.2 W
Power Factor (Fraction)	0.95
Connection	Internal connector
Cable	-
Number of products on MCB of 16 A type B	20

Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating with constant light output
Constant light output	Yes

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Post-top for diameter 60 to 76 mm
Optical cover shape	Convex lens

Optical cover finish	Clear
Overall length	529 mm
Overall width	265 mm
Overall height	154.5 mm
Effective projected area	0.032 m²
Dimensions (Height x Width x Depth)	155 x 265 x 529 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.37) SDCM<5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 75000 h	7.5 %
Lumen maintenance at median useful life* 75000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Order product name	BGS451 ECO43--2S/740 II MSO GR MSP CLO-L
Full product name	BGS451 ECO43--2S/740 II MSO GR MSP CLO-L
Full product code	871829141577000
Order code	910505005218
Material Nr. (12NC)	910505005218
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291415770
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291415770

Iridium LED Mini

Dimensional drawing

