



# MileWide LED gen2 small

## BRP435 GRN35-/740 II DM GR C6K T25

MileWide 2 side entry, LED GreenLine 3500 lm, Distribution medium

Many municipal authorities are embracing the benefits of contemporary outdoor lighting. These include a more attractive urban environment and increased comfort, safety and security for the public. Not to mention the positive impact on environmental protection and city branding. Together with Holscher Design, Philips has developed MileWide<sup>2</sup>, the successor to the highly popular MileWide family. Featuring a range of dedicated masts and brackets, the pure, clean design of MileWide<sup>2</sup> integrates perfectly with today's and tomorrow's cityscape. With its high-quality finish and high level of lighting performance, MileWide<sup>2</sup> is suitable for a wide range of applications, ranging from traffic roads to city centers. Multi-layer optics provide a uniform light distribution and reduced glare, enabling direct replacement of HID solutions without compromising on spacing, mounting height or light quality.

### Product data

General Information			
Lamp family code	GRN35 [LED GreenLine 3500 lm]		B10. Therefore, the median useful life (B50) value also represents the B10 value.
Light source replaceable	No	Light source engine type	LED
Number of gear units	1 unit	Product family code	BRP435 [MileWide 2 side entry]
Driver included	Yes	Lighting Technology	LED
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	Value ladder	Performance
		CE mark	Yes
		Warranty period	5 years
		Flammability mark	-
		ENEC mark	ENEC mark

## MileWide LED gen2 small

EU RoHS compliant	Yes
-------------------	-----

### Light Technical

Upward light output ratio	0
Luminous Flux	3,016 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	118 lm/W
Color rendering index (CRI)	>70
Number of light sources	40
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution medium

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.29 ms
Power Consumption	25.5 W
Power Factor (Fraction)	0.8
Connection	-
Cable	Cable 6.0 m without plug
Number of products on MCB of 16 A type B	5

### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Grey

Mounting device	Side-entry for diameter 40 to 48 mm
Optical cover shape	Convex lens
Optical cover finish	Silkscreen print black
Overall length	610 mm
Overall width	276 mm
Overall height	108 mm
Effective projected area	0.035 m²
Dimensions (Height x Width x Depth)	108 x 276 x 610 mm

### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.37) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L80

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

### Product Data

Order product name	BRP435 GRN35-/740 II DM GR C6K T25
Full product name	BRP435 GRN35-/740 II DM GR C6K T25
Full product code	871869610706500
Order code	10706500
Material Nr. (12NC)	910505016062
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696107065
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696107065

## MileWide LED gen2 small

### Dimensional drawing

