



MileWide LED gen2 large

BRP436 GRN116-/740 II DM SI CLO T25

MileWide 2 side entry large, LED GreenLine 11600 lm,
Distribution medium, Constant light output

Philips MileWide LED Gen2, developed together with Holscher Design, is the latest generation of our highly popular MileWide lighting family that features a range of dedicated masts and brackets. The pure, clean design of MileWide LED Gen2 integrates perfectly with the cityscapes of today and tomorrow. Available in two sizes, BPP435 (small) and BPP436 (large), this MileWide pole light will bring a touch of elegance and fluidity to any urban application (side entry versions: BRP435 and BRP436). Thanks to its advanced LED engine, and use of application-tailored optics, MileWide LED Gen2 delivers outstanding quality of light and light performance, enabling significant energy savings, yet still providing perfectly uniform light on the road. The luminaire is available with one or two Zhaga-D4i (ZD4i) System Ready (SR) sockets, which makes the luminaire future ready. This means MileWide LED Gen2 is ready to pair with advanced controls and lighting software applications such as Interact, or sensors such as the Philips Outdoor Sensor Bundle (OSB). Furthermore, each MileWide LED Gen2 luminaire is uniquely identifiable, thanks to the Signify Service tag app. By simply scanning a QR code, placed inside the door of the mast or directly on the luminaire, you can instantly access the configuration of the luminaire. This makes maintenance and programming operations faster and easier, and enables you to create a digital library of lighting assets and spare parts.

Product data

General Information		Number of gear units	
Lamp family code	GRN116 [LED GreenLine 11600 lm]	Driver included	Yes
Light source replaceable	No	Photocell	-

MileWide LED gen2 large

Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Light source engine type	LED
Product family code	BRP436 [MileWide 2 side entry large]
Lighting Technology	LED
Value ladder	Performance
Embedded control	Constant light output
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
EU RoHS compliant	Yes

Light Technical

Upward light output ratio	0
Luminous Flux	9,739 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	129 lm/W
Color rendering index (CRI)	>70
Number of light sources	64
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution medium

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	60.4 W
Average CLO power consumption	67.95 W
End CLO power consumption	75.5 W
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	82 W
Power Factor (Fraction)	0.8
Connection	Flying leads/wires
Cable	Cable 0.2 m with cable connector

Number of products on MCB of 16 A type 4
B

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
----------	----

Driver/power unit/transformer	Power supply unit regulating with constant light output
Control interface	-
Constant light output	Yes

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Silver
Mounting device	Side-entry for diameter 40 to 48 mm
Optical cover shape	Convex lens
Optical cover finish	Silkscreen print black
Overall length	734 mm
Overall width	306 mm
Overall height	125 mm
Effective projected area	0.046 m²
Dimensions (Height x Width x Depth)	125 x 306 x 734 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L100

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

Product Data

Order product name	BRP436 GRN116-/740 II DM SI CLO T25
Full product name	BRP436 GRN116-/740 II DM SI CLO T25
Full product code	871869611610400
Order code	910505016204
Material Nr. (12NC)	910505016204
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696116104

MileWide LED gen2 large

Numerator - Packs per outer box	1
EAN/UPC - Case	8718696116104

Dimensional drawing

