



MileWide LED gen2 large

BRP436 GRN185-/740 II DW GR LS-6 50% T25

MileWide 2 side entry large, LED GreenLine 18500 lm,
Distribution wide

Many municipal authorities are embracing the benefits of contemporary outdoor lighting. These include a more attractive urban environment and increased comfort, safety and security for the public. Not to mention the positive impact on environmental protection and city branding. Together with Holscher Design, Philips has developed MileWide², the successor to the highly popular MileWide family. Featuring a range of dedicated masts and brackets, the pure, clean design of MileWide² integrates perfectly with today's and tomorrow's cityscape. With its high-quality finish and high level of lighting performance, MileWide² is suitable for a wide range of applications, ranging from traffic roads to city centers. Multi-layer optics provide a uniform light distribution and reduced glare, enabling direct replacement of HID solutions without compromising on spacing, mounting height or light quality.

Product data

General Information			
Lamp family code	GRN185 [LED GreenLine 18500 lm]	maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Light source replaceable	No		
Number of gear units	1 unit		
Driver included	Yes	Light source engine type	LED
Photocell	-	Product family code	BRP436 [MileWide 2 side entry large]
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen	Lighting Technology	LED
		Value ladder	Performance
		Embedded control	LumiStep dimming 6 hours
		CE mark	Yes
		Warranty period	5 years

MileWide LED gen2 large

Flammability mark	-
ENEC mark	ENEC mark
EU RoHS compliant	Yes

Light Technical

Upward light output ratio	0
Luminous Flux	15,360 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	119 lm/W
Color rendering index (CRI)	>70
Number of light sources	64
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution wide

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	138 W
Power Factor (Fraction)	0.8
Connection	Flying leads/wires
Cable	Cable 0.2 m with cable connector
Number of products on MCB of 16 A type B	4

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Grey

Mounting device	Side-entry for diameter 40 to 48 mm
Optical cover shape	Convex lens
Optical cover finish	Silkscreen print black
Overall length	734 mm
Overall width	306 mm
Overall height	125 mm
Effective projected area	0.046 m²
Dimensions (Height x Width x Depth)	125 x 306 x 734 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

Product Data

Order product name	BRP436 GRN185-/740 II DW GR LS-6 50% T25
Full product name	BRP436 GRN185-/740 II DW GR LS-6 50% T25
Full product code	871869611622700
Order code	11622700
Material Nr. (12NC)	910505016216
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696116227
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696116227

MileWide LED gen2 large

Dimensional drawing

