



# SpeedStar

## BGP323 ECO227--3S/740 I DM FG AL SI

SpeedStar Large, LED EconomyLine 22700 lm, Distribution medium, Flat glass

Municipalities are under pressure to meet energy conservation goals by reducing their energy consumption and carbon footprint while complying with lighting norms and standards. Our SpeedStar LED luminaire addresses these fundamental issues and provides a solution to reduce the impact on our environment. SpeedStar is an energy-efficient luminaire requiring minimal maintenance and incorporating the easy-to-upgrade LEDGINE, which can be connected to lighting regulation systems for further energy savings. This carbon-neutral luminaire is the ideal solution for functional road and street lighting.

### Product data

General Information			
Lamp family code	ECO227 [LED EconomyLine 22700 lm]	Lighting Technology	LED
Light source replaceable	Yes	Embedded control	-
Number of gear units	Unit	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Photocell	-	Flammability mark	-
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	ENEC mark	ENEC mark
Light source engine type	LED	Glow-wire test	Temperature 650 °C, duration 5 s
Product family code	BGP323 [SpeedStar Large]	EU RoHS compliant	Yes
		Light Technical	
		Upwards light output ratio	0.03
		Luminous Flux	23,800 lm
		Standard tilt angle post-top	5°
		Standard tilt angle side entry	0°
		Correlated Colour Temperature	4000 K

Luminous efficacy (rated) (nom.)	124 lm/W
Colour rendering index (CRI)	70
Light source colour	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution medium

#### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	192 W
Power Factor (Fraction)	0.8
Connection	-
Cable	-
Number of products on MCB of 16 A type B	3

#### Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating
Control interface	-
Constant light output	No

#### Mechanical and Housing

Housing material	Aluminium
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Glass
Fixation material	Aluminium
Housing Colour	Silver
Mounting device	Universal for diameter 42 to 76 mm
Optical cover/lens shape	Convex lens
Optical cover/lens finish	Clear
Overall length	1,021 mm
Overall width	400 mm

Overall height	129 mm
Effective projected area	0.041 m²
Dimensions (height x width x depth)	129 x 400 x 1021 mm
Parts colour	All parts coloured

#### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level up to 6 kV differential mode and 6 kV common mode
Protection class IEC	Safety class I

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.370) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	7.5 %
Lumen maintenance at median useful life* 75000 h	L80

#### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

#### Product Data

Order product name	BGP323 ECO227--3S/740 I DM FG AL SI
Full product name	BGP323 ECO227--3S/740 I DM FG AL SI
Full EOC	871829134824500
Order code	34824500
Material no. (12 NC)	910505016376
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291348245
Numerator – packs per outer box	1
EAN/UPC - Case	8718291348245

## Dimensional drawing

