



SpeedStar

BGP322 ECO142--3S/740 I DM FG AL SI

SpeedStar Medium, LED EconomyLine 14200 lm, Distribution medium, Flat glass

Municipalities are under pressure to meet energy conservation goals by reducing their energy consumption and carbon footprint while complying with lighting norms and standards. Our SpeedStar LED luminaire addresses these fundamental issues and provides a solution to reduce the impact on our environment. SpeedStar is an energy-efficient luminaire requiring minimal maintenance and incorporating the easy-to-upgrade LEDGINE, which can be connected to lighting regulation systems for further energy savings. This carbon-neutral luminaire is the ideal solution for functional road and street lighting.

Product data

General Information			
Lamp family code	ECO142 [LED EconomyLine 14200 lm]	Embedded control	-
Light source replaceable	Yes	CE mark	Yes
Number of gear units	1 unit	Warranty period	5 years
Driver included	Yes	Flammability mark	-
Photocell	-	ENEC mark	ENEC mark
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test	Temperature 650 °C, duration 5 s
Light source engine type	LED	EU RoHS compliant	Yes
Product family code	BGP322 [SpeedStar Medium]	Light Technical	
Lighting Technology	LED	Upward light output ratio	0.03
		Luminous Flux	14,900 lm
		Standard tilt angle posttop	5°
		Standard tilt angle side entry	0°
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	125 lm/W

Color rendering index (CRI)	70
Number of light sources	56
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution medium

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	119 W
Power Factor (Fraction)	0.8
Connection	-
Cable	-
Number of products on MCB of 16 A type B	6

Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Silver
Mounting device	Universal for diameter 42 to 76 mm
Optical cover shape	Convex lens
Optical cover finish	Clear
Overall length	768 mm
Overall width	394 mm

Overall height	129 mm
Effective projected area	0.034 m²
Dimensions (Height x Width x Depth)	129 x 394 x 768 mm
Parts color	All parts colored

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 6 kV common mode
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.370) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 75000 h	7.5 %
Lumen maintenance at median useful life* 75000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

Product Data

Order product name	BGP322 ECO142--3S/740 I DM FG AL SI
Full product name	BGP322 ECO142--3S/740 I DM FG AL SI
Full product code	871829133599300
Order code	910505016412
Material Nr. (12NC)	910505016412
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291335993
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291335993

Dimensional drawing

