



UrbanSky

BSP390 GRN49--3S/740 II DSN-L DGR CLO-LS

UrbanSky, LED GreenLine 4900 lm, Power supply unit regulating, Distribution symmetrical narrow lengthwise

UrbanSky is the first dedicated catenary luminaire to bring together state-of-the-art LED technology and innovative design. It is a prime example of how high-quality LED light and ground-breaking design can increase safety and comfort, with particular emphasis on optical guidance. Designed together with renowned agency podpoddesign, UrbanSky is a contemporary and future-proof solution that will enhance any city's identity. Its LEDGINE module offers significant energy savings, while its neutral-white light and good color rendering create a relaxed lighting mood and increase safety. Multi-layer optics provide a uniform light distribution with reduced glare, allowing direct replacement of HID solutions without compromising on spacing, mounting height or light quality. And the energy-efficient LEDGINE is delivered ready for tool-less serviceability/upgrades, ensuring savings far into the future.

Product data

General Information			
Lamp family code	GRN49 [LED GreenLine 4900 lm]	Product family code	BSP390 [UrbanSky]
Light source replaceable	Yes	Lighting Technology	LED
Driver included	Yes	Embedded control	Constant light output and LumiStep dimming 6 hours
Photocell	-	CE mark	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Flammability mark	-
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 30 s
		EU RoHS compliant	No

Light Technical	
Luminous Flux	5,100 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	131 lm/W
Number of light sources	32
Light source color	740 neutral white
Optical cover type	Acrylic bowl/cover frosted
Optic type outdoor	Distribution symmetrical narrow lengthwise

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	39 W
Cable	-

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit regulating

Mechanical and Housing	
Housing Material	Aluminum
Housing Color	Dark gray
Mounting device	Mounting bracket adjustable
Parts color	All parts colored

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]

Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class II

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L100

Application Conditions	
Performance ambient temperature Tq	25 °C

Product Data	
Order product name	BSP390 GRN49--3S/740 II DSN-L DGR CLO-LS
Full product name	BSP390 GRN49--3S/740 II DSN-L DGR CLO-LS
Full product code	871829140686000
Order code	910505016706
Material Nr. (12NC)	910505016706
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291406860
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291406860

Dimensional drawing



