



UrbanSky

BSP390 ECO93--3S/830 II DSN-C DGR C5K T2

UrbanSky, LED EconomyLine 9300 lm, Power supply unit regulating, Distribution symmetrical narrow crosswise

UrbanSky is the first dedicated catenary luminaire to bring together state-of-the-art LED technology and innovative design. It is a prime example of how high-quality LED light and ground-breaking design can increase safety and comfort, with particular emphasis on optical guidance. Designed together with renowned agency podpoddesign, UrbanSky is a contemporary and future-proof solution that will enhance any city's identity. Its LEDGINE module offers significant energy savings, while its neutral-white light and good color rendering create a relaxed lighting mood and increase safety. Multi-layer optics provide a uniform light distribution with reduced glare, allowing direct replacement of HID solutions without compromising on spacing, mounting height or light quality. And the energy-efficient LEDGINE is delivered ready for tool-less serviceability/upgrades, ensuring savings far into the future.

Product data

General Information			
Lamp family code	ECO93 [LED EconomyLine 9300 lm]	Product family code	BSP390 [UrbanSky]
Light source replaceable	Yes	Lighting Technology	LED
Driver included	Yes	Embedded control	-
Photocell	-	CE mark	Yes
Flammability mark	-	Flammability mark	-
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 30 s
		EU RoHS compliant	No
Light Technical			
Luminous Flux	9,800 lm		

Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	105 lm/W
Color rendering index (CRI)	80
Number of light sources	48
Light source color	830 warm white
Optical cover type	Acrylic bowl/cover frosted
Optic type outdoor	Distribution symmetrical narrow crosswise

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	93 W
Cable	Cable 5.0 m without plug

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating

Mechanical and Housing

Housing Material	Aluminum
Housing Color	Dark gray
Mounting device	Mounting bracket adjustable
Parts color	All parts colored

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Init. Color Rendering Index Tolerance	+/-2
---------------------------------------	------

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 75000 h	7.5 %
Lumen maintenance at median useful life* 75000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Order product name	BSP390 ECO93--3S/830 II DSN-C DGR C5K T2
Full product name	BSP390 ECO93--3S/830 II DSN-C DGR C5K T2
Full product code	871829141189500
Order code	910505016743
Material Nr. (12NC)	910505016743
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291411895
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291411895

Dimensional drawing



