



# CitySoul gen2 LED Large

**BPP531 GRN165-/740 I DM FG CO GR D9 T35**

CitySoul gen2 Large, LED GreenLine 16500 lm, Distribution medium, Flat glass

CitySoul gen2 LED is one of the most versatile and inspirational urban street lighting families designed by Philips to date. This highly efficient range delivers excellent lighting levels whilst also providing the right ambiance for all urban application areas, from the outskirts of the city right through to the city center. By evolving the modularity of the CitySoul family and adding new innovations like the Lyre and the Accent bracket, Philips has made this range the ideal toolbox for every urban context. The design is flatter, completely round, and the transitions with the spigot and bracket entirely flush, thereby giving your cityscape a coherent, elegant and discreet identity. Designed around its LED engine, CitySoul gen2 LED is highly efficient and easy to maintain. It comes in two sizes and is suitable for side-entry, post-top, catenary and suspended mounting.

## Product data

General Information		Lighting Technology	
Lamp family code	GRN165 [LED GreenLine 16500 lm]	Lighting Technology	LED
Light source replaceable	Yes	Value ladder	Performance
Number of gear units	Unit	Embedded control	-
Driver included	Yes	CE mark	Yes
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components	Warranty period	5 years
Light source engine type	LED	Flammability mark	-
Product family code	BPP531 [CitySoul gen2 Large]	ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 30 s
		EU RoHS compliant	Yes

# CitySoul gen2 LED Large

<b>Light Technical</b>	
Upwards light output ratio	0.03
Luminous Flux	13,453 lm
Standard tilt angle post-top	0°
Standard tilt angle side entry	0°
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	120 lm/W
Colour rendering index (CRI)	>70
Light source colour	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution medium
<b>Operating and Electrical</b>	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	112 W
Power Factor (Fraction)	0.8
Connection	-
Cable	-
Number of products on MCB of 16 A type B 11	
<b>Temperature</b>	
Ambient temperature range	-40 to +50 °C
<b>Controls and Dimming</b>	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
<b>Mechanical and Housing</b>	
Housing material	Aluminium
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Aluminium
Housing Colour	Grey
Mounting device	Spigot for diameter 60 to 76 mm
Optical cover/lens shape	Convex lens
Optical cover/lens finish	Mask (anti-glare)

Overall length	720 mm
Overall width	628 mm
Overall height	99 mm
Effective projected area	0.028 m²
Dimensions (height x width x depth)	99 x 628 x 720 mm
Parts colour	Cover painted
<b>Approval and Application</b>	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level up to 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.37) SDCM<5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
<b>Over Time Performance (IEC Compliant)</b>	
Driver failure rate at 5,000 hours	0.15 %
<b>Application Conditions</b>	
Maximum dim level	10%
<b>Product Data</b>	
Order product name	BPP531 GRN165-/740 I DM FG CO GR D9 T35
Full product name	BPP531 GRN165-/740 I DM FG CO GR D9 T35
Full EOC	871869661348100
Order code	61348100
Material no. (12 NC)	910505016888
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696613481
Numerator – packs per outer box	1
EAN/UPC – Case	8718696613481

CitySoul gen2 LED Large

Dimensional drawing

