



# CitySoul gen2 LED Mini

## BRP530 LED55/740 II DM FG CO GR

CitySoul gen2 Mini, LED GreenLine 5500 lm, Distribution medium, Flat glass

CitySoul gen2 LED is one of the most versatile and inspirational urban street lighting families designed by Philips to date. This highly efficient range delivers excellent lighting levels whilst also providing the right ambiance for all urban application areas, from the outskirts of the city right through to the city center. By evolving the modularity of the CitySoul family and adding new innovations like the Lyre and the Accent bracket, Philips has made this range the ideal toolbox for every urban context. The design is flatter, completely round, and the transitions with the spigot and bracket entirely flush, thereby giving your cityscape a coherent, elegant and discreet identity. Designed around its LED engine, CitySoul gen2 LED is highly efficient and easy to maintain. It comes in two sizes and is suitable for side-entry, post-top, catenary and suspended mounting.

### Product data

General Information		Lighting Technology	
Lamp family code	GRN55 [LED GreenLine 5500 lm]	Value ladder	Performance
Light source replaceable	Yes	Embedded control	-
Number of gear units	1 unit	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components	Flammability mark	-
Light source engine type	LED	ENEC mark	ENEC mark
Product family code	BRP530 [CitySoul gen2 Mini]	EU RoHS compliant	Yes

## CitySoul gen2 LED Mini

<b>Light Technical</b>	
Upward light output ratio	0.03
Luminous Flux	4,704 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	145 lm/W
Color rendering index (CRI)	>70
Number of light sources	1
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution medium

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	45 A
Inrush time	0.285 ms
Power Consumption	32.5 W
Power Factor (Fraction)	0.95
Connection	-
Cable	-
Number of products on MCB of 16 A type B	10

### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Side-entry for diameter 48 to 60 mm

Optical cover shape	Convex lens
Optical cover finish	Mask (anti-glare)
Overall length	644 mm
Overall width	538 mm
Overall height	101 mm
Effective projected area	0.025 m²
Dimensions (Height x Width x Depth)	101 x 538 x 644 mm
Parts color	Cover painted

### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.370) SDCM<5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.15 %
-------------------------------	--------

### Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

### Product Data

Order product name	BRP530 LED55/740 II DM FG CO GR
Full product name	BRP530 LED55/740 II DM FG CO GR
Full product code	871869661391700
Order code	61391700
Material Nr. (12NC)	910505016933
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696613917
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696613917

CitySoul gen2 LED Mini

Dimensional drawing

