



# CityCharm Cordoba

## BDS490 GRN20-/740 II S GRB DF GR MSP CLO

CityCharm Cordoba, LED GreenLine 2000 lm, Symmetrical, Marine salt protected coating, Constant light output and LumiStep dimming 8 hours

The Philips CityCharm range is designed for use in urban areas where comfortable lighting, ambience, and design play an important role. It offers three iconic, timeless designs: CityCharm cordoba (BDS490), CityCharm cone (BDS491), and CityCharm fluid (BDS492) along with a range of decorative and practical accessories. This enables you to create a lighting solution that carries the signature of your municipality, both by day and by night. Whether you specify cordoba, cone or fluid LED lights, CityCharm provides high visual comfort while maintaining excellent performance. It offers a choice of two innovative Philips Lighting technologies: GentleBeam, which maximizes visual comfort, or ClearGuide (cordoba or cone), which optimizes vertical illumination and visual guidance. To personalize your CityCharm lighting solution further, decorative accessories for this range make it possible to define the volume of the bowl and change its appearance. To personalize your CityCharm lighting solution further, decorative accessories for this range make it possible to define the volume of the bowl and change its appearance. A variety of dedicated brackets and masts are also available to enable you to reshape your residential areas and city centers in the most elegant way imaginable.

### Product data

General Information		Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Lamp family code	GRN20 [LED GreenLine 2000 lm]		
Light source replaceable	Yes		
Number of gear units	1 unit	Light source engine type	LED
Gear	EB [Electronic]	Product family code	BDS490 [CityCharm Cordoba]
Driver included	Yes	Lighting Technology	LED

## CityCharm Cordoba

Value ladder	Performance
Embedded control	Constant light output and LumiStep dimming 8 hours
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes

### Light Technical

Upward light output ratio	0.03
Luminous Flux	1,699 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	106 lm/W
Color rendering index (CRI)	≥70
Number of light sources	8
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	360°
Optic type outdoor	Symmetrical

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	12.8 W
Average CLO power consumption	14.4 W
End CLO power consumption	16 W
Inrush current	28 A
Inrush time	15 ms
Power Consumption	16 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires
Cable	Cable 6.0 m without plug
Number of products on MCB of 16 A type B	32

### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating with constant light output
Control interface	-
Constant light output	Yes

### Mechanical and Housing

Housing Material	Aluminum
------------------	----------

Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Spigot for diameter 60 mm
Optical cover shape	Hemispherical
Optical cover finish	Clear
Overall height	529 mm
Overall diameter	556 mm
Effective projected area	0.1124 m²

### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.380, 0.370) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.05 %
-------------------------------	--------

### Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

### Product Data

Order product name	BDS490 GRN20-/740 II S GRB DF GR MSP CLO
Full product name	BDS490 GRN20-/740 II S GRB DF GR MSP CLO
Full product code	871869692114200
Order code	910505017130
Material Nr. (12NC)	910505017130
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696921142
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696921142

## CityCharm Cordoba

### Dimensional drawing

