



CityCharm Cordoba

BDS490 GRN60-/830 I DM GRB DF-S GR D9 H0

CityCharm Cordoba, LED GreenLine 6000 lm, Distribution medium

CityCharm Cordoba is designed for use in urban areas where comfortable lighting, ambiance and design play an important role. Its unobtrusive appearance makes it a timeless, future-proof luminaire that is ideal for residential areas, parks, footpaths and cycle lanes, where visual comfort and maximum efficiency are key. CityCharm offers a choice of two iconic designs (Cordoba and Cone) and various accessories, enabling you to create a lighting solution that carries your signature, both by day and by night. CityCharm luminaires are also available as a complete set, with a choice of dedicated poles and brackets.

Product data

General Information		Warranty period	
Lamp family code	GRN60 [LED GreenLine 6000 lm]	Flammability mark	-
Light source replaceable	Yes	ENEC mark	ENEC mark
Number of gear units	1 unit	Glow-wire test	Temperature 650 °C, duration 30 s
Gear	EB [Electronic]	EU RoHS compliant	Yes
Driver included	Yes	Light Technical	
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components	Upward light output ratio	0.03
Light source engine type	LED	Luminous Flux	5,092 lm
Product family code	BDS490 [CityCharm Cordoba]	Standard tilt angle posttop	0°
Lighting Technology	LED	Standard tilt angle side entry	0°
Value ladder	Performance	Correlated Color Temperature (Nom)	3000 K
Embedded control	-	Luminous Efficacy (rated) (Nom)	118 lm/W
CE mark	Yes	Color rendering index (CRI)	≥80
		Number of light sources	40

CityCharm Cordoba

Light source color	830 warm white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	360°
Optic type outdoor	Distribution medium

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	80 A
Inrush time	15 ms
Power Consumption	43 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires
Cable	Cable 0.2 m without plug
Number of products on MCB of 16 A type B	11

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Spigot for diameter 60 mm
Optical cover shape	Hemispherical
Optical cover finish	Clear
Overall height	529 mm
Overall diameter	556 mm

Effective projected area	0.1124 m²
--------------------------	-----------

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.430, 0.400) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.05 %
-------------------------------	--------

Application Conditions

Maximum dim level	20%
-------------------	-----

Product Data

Order product name	BDS490 GRN60-/830 I DM GRB DF-S GR D9 H0
Full product name	BDS490 GRN60-/830 I DM GRB DF-S GR D9 H0
Full product code	871869692126500
Order code	92126500
Material Nr. (12NC)	910505017142
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696921265
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696921265

Dimensional drawing



