



# CityCharm Cone

BDS491 LWFP GRN40-/740 I DM GRB GR CLO C

CityCharm Cone, LED GreenLine 4000 lm, Distribution medium, Constant light output

CityCharm Cone is designed for use in urban areas where comfortable lighting, ambiance and design play an important role. Its unobtrusive appearance makes it a timeless, future-proof luminaire that is ideal for residential areas, parks, footpaths and cycle lanes, where visual comfort and maximum efficiency are key. CityCharm offers a choice of two iconic designs (Cone and Cordoba) and various accessories, enabling you to create a lighting solution that carries your signature, both by day and by night. CityCharm luminaires are also available as a complete set, with a choice of dedicated poles and brackets.

## Product data

General Information		Warranty period	
Lamp family code	GRN40 [LED GreenLine 4000 lm]	Flammability mark	-
Light source replaceable	Yes	ENEC mark	ENEC mark
Number of gear units	Unit	Glow-wire test	Temperature 650 °C, duration 30 s
Gear	EB [Electronic]	EU RoHS compliant	Yes
Driver included	Yes	Light Technical	
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components	Upwards light output ratio	0.03
Light source engine type	LED	Luminous Flux	3,396 lm
Product family code	BDS491 [CityCharm Cone]	Standard tilt angle post-top	0°
Lighting Technology	LED	Standard tilt angle side entry	0°
Value ladder	Performance	Correlated Colour Temperature	4000 K
Embedded control	Constant light output	Luminous efficacy (rated) (nom.)	117 lm/W
CE mark	Yes	Colour rendering index (CRI)	≥70
		Light source colour	740 neutral white

# CityCharm Cone

Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	360°
Optic type outdoor	Distribution medium

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	23.2 W
Average CLO power consumption	26.1 W
End CLO power consumption	29 W
Inrush current	27 A
Inrush time	15 ms
Power Consumption	29 W
Power Factor (Fraction)	0.9
Connection	Flying leads/cables
Cable	Cable 0.2 m without plug
Number of products on MCB of 16 A type B 32	

## Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating with constant light output
Control interface	GPRS network
Constant light output	Yes

## Mechanical and Housing

Housing material	Aluminium
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Aluminium
Housing Colour	Grey
Mounting device	Spigot for diameter 76 mm
Optical cover/lens shape	Hemispherical
Optical cover/lens finish	Clear
Overall height	529 mm

Overall diameter	556 mm
Effective projected area	0.1155 m²

## Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Luminaire surge protection level up to 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.380, 0.370) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

## Over Time Performance (IEC Compliant)

Driver failure rate at 5,000 hours	0.05 %
------------------------------------	--------

## Application Conditions

Maximum dim level	10%
-------------------	-----

## Product Data

Order product name	BDS491 LWFP GRN40-/740 I DM GRB GR CLO C
Full product name	BDS491 LWFP GRN40-/740 I DM GRB GR CLO C
Full EOC	871869692135700
Order code	92135700
Material no. (12 NC)	910505017151
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696921357
Numerator – packs per outer box	1
EAN/UPC – Case	8718696921357

CityCharm Cone

Dimensional drawing

