



CityCharm Cone

BDS491 CG25-/740 II S GR D11 76

CityCharm Cone, 15, LED module, system flux 2500 lm, LED, 740 neutral white, Power supply unit regulating, 220 to 240 V, 50 to 60 Hz, Safety class II, Symmetrical, Polycarbonate bowl/cover, Gray, Luminaire surge protection level until 6 kV differential mode and 8 kV common mode, Cable 0.2 m without plug, Spigot for diameter 76 mm

The Philips CityCharm range is designed for use in urban areas where comfortable lighting, ambience, and design play an important role. It offers three iconic, timeless designs: CityCharm cordoba (BDS490), CityCharm cone (BDS491), and CityCharm fluid (BDS492) along with a range of decorative and practical accessories. This enables you to create a lighting solution that carries the signature of your municipality, both by day and by night. Whether you specify cordoba, cone or fluid LED lights, CityCharm provides high visual comfort while maintaining excellent performance. It offers a choice of two innovative Philips Lighting technologies: GentleBeam, which maximizes visual comfort, or ClearGuide (cordoba or cone), which optimizes vertical illumination and visual guidance. To personalize your CityCharm lighting solution further, decorative accessories for this range make it possible to define the volume of the bowl and change its appearance. A variety of dedicated brackets and masts are also available to enable you to reshape your residential areas and city centers in the most elegant way imaginable.

Product data

General Information			
Lamp family code	CG25 [LED module, system flux 2500 lm]	Gear	EB [Electronic]
Light source replaceable	Yes	Driver included	Yes
Number of gear units	1 unit		

CityCharm Cone

Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Light source engine type	LED
Product family code	BDS491 [CityCharm Cone]
Lighting Technology	LED
Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

Light Technical

Upward light output ratio	0.03
Luminous Flux	2,140 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	107 lm/W
Color rendering index (CRI)	≥70
Number of light sources	15
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	360°
Optic type outdoor	Symmetrical

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	27 A
Inrush time	15 ms
Power Consumption	20 W
Power Factor (Fraction)	0.96
Connection	Flying leads/wires
Cable	Cable 0.2 m without plug
Number of products on MCB of 16 A type B	26

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
------------------	----------

Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Gray
Mounting device	Spigot for diameter 76 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall height	529 mm
Overall diameter	556 mm
Effective projected area	0.1155 m²

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.380, 0.370) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.05 %
Lumen maintenance at median useful life*	L93
100000 h	

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

Product Data

Order product name	BDS491 CG25-/740 II S GR D11 76
Full product name	BDS491 CG25-/740 II S GR D11 76
Full product code	871869693921500
Order code	910505017426
Material Nr. (12NC)	910505017426
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696939215
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696939215

CityCharm Cone

Dimensional drawing

