



Maxos TL-D, trapeze reflectors and optics

4MX093 2 58 L-T WH

MAXOS LLT8, 2, 58 W

The sturdy trapeze reflectors for TL-D are designed for standard applications in industry, supermarkets, and shops. They are made of steel with a white or silver coating. The reflectors are optimised for electrical units holding 1 or 2 TL-D lamps and provide an excellent light output ratio. There are basic trapeze reflectors without a mirror inlay and trapeze reflectors with different aluminium mirror inlays. These are suitable for wide beam, narrow beam, and asymmetrical wall washing light distributions. Moreover, perforated and slotted trapeze reflectors, without mirror inlays, can be ordered as design elements or to create an indirect uplighting effect. For glare reduction, the trapeze reflector can be equipped with a steel louver that has a white or silver coating. To use emergency lighting by separately connected orientation light units (E27-sockets), special trapeze reflectors with a cut-off must be selected. The length of this reflector corresponds with that of the 58 W trunking length. A 36 W-electrical unit plus the orientation light unit will fill this length. The reflectors are fixed on the electrical units via a simple click-in. The reflectors can also be connected to each other in a line without additional coupling pieces, as they are delivered with an integrated connection side at one end of the reflector. At the beginning and the end of the lightline end plates, as accessories, are available.

Product data

General Information	
Accessory color	White
Product family code	4MX093 [MAXOS LLT8]


Light Technical	
Number of light sources	2

Maxos TL-D, trapeze reflectors and optics

Operating and Electrical	
Power Consumption	58 W
Approval and Application	
Ingress protection code	-
Product Data	
Order product name	4MX093 2 58 L-T WH
Full product name	4MX093 2 58 L-T WH

Full product code	403073261460899
Order code	61460899
Material Nr. (12NC)	910605103626
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732614608
Numerator - Packs per outer box	6
EAN/UPC - Case	4030732215690

Dimensional drawing



Product
4MX093 2 58 L-T WH

