



Maxos TL-D, trapeze reflectors and optics

4MX092 2 58 T-NB WH

MAXOS R T8, 2, 58 W

The sturdy trapeze reflectors for TL-D are designed for standard applications in industry, supermarkets, and shops. They are made of steel with a white or silver coating. The reflectors are optimised for electrical units holding 1 or 2 TL-D lamps and provide an excellent light output ratio. There are basic trapeze reflectors without a mirror inlay and trapeze reflectors with different aluminium mirror inlays. These are suitable for wide beam, narrow beam, and asymmetrical wall washing light distributions. Moreover, perforated and slotted trapeze reflectors, without mirror inlays, can be ordered as design elements or to create an indirect uplighting effect. For glare reduction, the trapeze reflector can be equipped with a steel louver that has a white or silver coating. To use emergency lighting by separately connected orientation light units (E27-sockets), special trapeze reflectors with a cut-off must be selected. The length of this reflector corresponds with that of the 58 W trunking length. A 36 W-electrical unit plus the orientation light unit will fill this length. The reflectors are fixed on the electrical units via a simple click-in. The reflectors can also be connected to each other in a line without additional coupling pieces, as they are delivered with an integrated connection side at one end of the reflector. At the beginning and the end of the lightline end plates, as accessories, are available.

Product data

| General Information | | Light Technical | |
|---------------------|---------------------|-------------------------|---|
| Accessory color | White | Number of light sources | 2 |
| Product family code | 4MX092 [MAXOS R T8] | | |

Maxos TL-D, trapeze reflectors and optics


| Operating and Electrical | |
|--------------------------|------|
| Power Consumption | 58 W |

| Approval and Application | |
|--------------------------|-------------------------|
| Ingress protection code | IP20 [Finger-protected] |

| Product Data | |
|--------------------|---------------------|
| Order product name | 4MX092 2 58 T-NB WH |
| Full product name | 4MX092 2 58 T-NB WH |

| | |
|---------------------------------|-----------------|
| Full product code | 403073253932199 |
| Order code | 53932199 |
| Material Nr. (12NC) | 910605110726 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 4030732539321 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 4030732108930 |

Dimensional drawing



Product

4MX092 2 58 T-NB WH

