



# Maxos TL5, trapeze reflectors and optics

4MX693 1/2 54 L-T WH

MAXOS LLT5, 54 W

The sturdy trapeze reflectors for TL5 are designed first for applications in supermarkets, shops and industry. They are made of steel, with a white or silver finish. The reflectors are made for electrical units holding one or two TL5 lamps 54, 49 or 80 W and provide an excellent light output ratio. There are basic trapeze reflectors without an additional mirror inlay and trapeze reflectors with dedicated aluminum mirror inlays. These are designed for narrow-beam or medium-beam light distributions, asymmetrical wall-washing light distribution on request. Moreover perforated reflectors giving a more airy design and slotted trapeze reflectors (without mirror inlays) can be ordered to create an indirect uplighting effect. For glare reduction, the trapeze reflector can be equipped with a white steel louver (L-T). The reflectors are fixed to the electrical units via a simple click-in. The reflectors can be connected to each other in a line with a connection piece at one end of the reflector coming with the reflector. End plates for the beginning and the end of the light line, are available as accessories.

## Product data


General Information		Approval and Application	
Accessory color	White	Ingress protection code	IP63 [Dust penetration-protected, rain/spray-proof]
Product family code	4MX693 [MAXOS LLT5]	Product Data	
Operating and Electrical		Full product code	403073263516099
Power Consumption	54 W	Order product name	4MX693 1/2 54 L-T WH
		Order code	910605125726
		Numerator - Quantity Per Pack	1

# Maxos TL5, trapeze reflectors and optics

Numerator - Packs per outer box	6
Material Nr. (12NC)	910605125726
Full product name	4MX693 1/2 54 L-T WH
EAN/UPC - Case	4030732230334

EAN/UPC - Product/Case	4030732635160
------------------------	---------------

## Dimensional drawing



Product
4MX693 1/2 54 L-T WH

