



Maxos TL-D, decorative solutions

4MX693 1/2 54 L-D WH

MAXOS LLT5, 54 W

The Wing optic is a reflector solution creating soft indirect light without glare and is ideal for office and shop applications. It is made of white powder-coated steel. A perforated curved sheet hides the lamps. The reflectors are available for electrical units holding 1 or 2 TL-D lamps. The 2-lamp version of the Wing optic must be used with special electrical units (lamp holder F32 mm) for TL-D lamps. TL5 solutions are available on request. The Wing optic is fixed to the electrical unit via a simple click-in. The reflectors can be connected to each other without additional coupling pieces, as they are delivered with an integrated connection side at one end of the reflector. Decorative end-plates for the beginning and end of the light line are available as accessories.

Product data

General Information		Order product name	4MX693 1/2 54 L-D WH
Accessory color	White	Order code	910605125926
Product family code	4MX693 [MAXOS LLT5]	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	6
Operating and Electrical		Material Nr. (12NC)	910605125926
Power Consumption	54 W	Full product name	4MX693 1/2 54 L-D WH
		EAN/UPC - Case	4030732231270
Approval and Application		EAN/UPC - Product/Case	4030732636327
Ingress protection code	-		
Product Data			
Full product code	403073263632799		